





For Professionals... Since 1857®

WHERE TO BUY

Search Klein

[Home](#) » [Catalog](#) » [Insulated Tools](#) » [Insulated Screwdrivers](#) » [Insulated Square-Recess-Tip \(Round Shank\)](#)

Insulated #2 Square-Recess Screwdriver - 4" Shank



Cat. No. 662-4-INS

Product Features

*1000V rated for safety.
Durable, flame-retardant, molded dual-layer insulation meets or exceeds all ASTM and IEC standards for insulated tools.
Cushion-Grip handle for greater torque and comfort.
Custom US-made steel tool.
Made in the USA.
This item replaces the 666-INS.*

BUY NOW

FIND RETAILER



Specifications

Downloads

Warnings

Shank Length: 4" (102 mm)

Overall Length: 8-5/16" (211 mm)

Point Size: #2

Weight (lbs.): .21

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)



© 2013 Klein Tools, Inc. • All Rights Reserved • 450 Bond Street • Lincolnshire, IL 60069 • USA • phone: 800-553-4676 • fax: 800-553-4876
[Privacy Policy](#) | [Terms & Conditions](#)