



[Home](#) » [Catalog](#) » [Insulated Tools](#) » [Insulated Pliers](#) » [Insulated Long-Nose Pliers](#)

6" Insulated Standard Long-Nose Pliers - Side-Cutting



Cat. No. D203-6-INS

Product Features

Individually tested to exceed the IEC 60900 and ASTM F1505 standards, for insulated tools, and clearly marked with the official 1000-volt rating symbol.

Two layers of insulation provide protection against electric shock. Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool.

A flame retardant, impact-resistant, bright orange outer coating. Curved handles provide greater tool control.

Integral guards help prevent hand contact with conductive parts.

BUY NOW

FIND RETAILER



Specifications

Downloads

Warnings

Jaw Thickness: 3/8"

Handle Finish: insulated

Point Thickness: 3/32"

Handle Color: orange

Overall Length: 6-7/8"

Jaw Length: 1-15/16"

Knife Length: 1/2"

Jaw Width: 11/16"

Weight (lbs.): .35

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)



© 2013 Klein Tools, Inc. • All Rights Reserved • 450 Bond Street • Lincolnshire, IL 60069 • USA • phone: 800-553-4676 • fax: 800-553-4876

[Privacy Policy](#) | [Terms & Conditions](#)