



760049957 | M2000A-24 1U

CommScope M2000 U/UTP Modular Panel 1U, 24 port angled

- Available for use with the DYMO® labeling solution

Dimensions

Depth, with cable management	5.00 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	3 5 5e 6 6A
-------------------	---------------------

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	Passive
Total Ports, quantity	24
Product Type	Panel, modular
Brand	CommScope®
Color	Black
Package, quantity	1
Rack Type	EIA 19 in
Rack Units	1

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
---------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

