

**18V Lithium-Ion**  
**GATOR®**  
**ES32L & ES32FL**

**Battery-Powered Cable Cutters**



**LED Work  
Light**



**Battery  
LED Monitor**

***FAST CUTS...***

Greenlee now offers two versions of the very popular ES32 type cutter. The ES32L cuts standard stranded copper and aluminum power cables while the ES32FL cuts fine stranded flexible copper cables. Locomotive cable, welding cable, wind turbine cable, battery cable and marine engine cable are examples of the flexible cables that the ES32L is designed to cut. Both tools are lightweight, easy to maneuver into tight locations, and have scissor style blades that make it easy to get around cables. Plus, both tools utilize the new advanced technology Greenlee "L" series platform with state-of-the art 18 volt Lithium-Ion battery power.

## Features

# ES32L



# ES32FL

- Designed for cutting standard stranded copper and aluminum power cables.
- State-of-the art 18V lithium ion (Li-ion) battery provides 70% more cycles per charge and faster cycle times.
- LED light provides the operator with the battery charge and tool maintenance status.
- Small size makes the ES32L an excellent tool for use inside panel boxes.
- In-line tool style is light weight and very easy to control.
- One trigger controls all tool functions.
- Cutting head rotates 350°.
- Tools automatically retract when the cutting cycle is complete.
- Overmolded tacky grip areas make gripping the tool easier and more comfortable.
- LED work light illuminates dark work areas.
- Greenlee battery-powered crimping tools now use bio-degradable oil.
- Smart chargers control the charging current, charging voltage and battery temperature to maximize battery life.
- Available with 120V, 12V or 230V battery charger or with 120V or 230V corded adapter in place of batteries and charger.

## Specifications

### SPECIFICATIONS

Capacity	500 kcmil (240 mm <sup>2</sup> ) Cu or Al cable
Battery Voltage	18V 1.5 Ah Li-ion
Length	14-5/8" (372 mm)
Weight	4.4 lbs. (2.0 kg)
Battery Charge Time	30 minutes
Est. Cycles Per Charge	200 (500kcmil cable requires 2 cycles per cut)

## Order Information

CAT. NO.	UPC NO.	DESCRIPTION	R = REPLACEMENT PART	A = ACCESSORY
ES32L11	52107	ES32L Battery-Powered Cable Cutter with 120 V Charger		
ES32L12	52108	ES32L Battery-Powered Cable Cutter with 12 V Charger		
ES32L22	52116	ES32L Battery-Powered Cable Cutter with 230 V Charger		
ES32L120	52117	ES32L Battery-Powered Cable Cutter with 120V AC Adapter		
ES32L230	52118	ES32L Battery-Powered Cable Cutter with 230V AC Adapter		
12092	12092	R Movable Blade		
12093	12093	R Fixed Blade		
52177	52177	R 18V 1.5 Ah Li-ion		
25752	25752	R Carrying Case		
52178	52178	R 120V Charger		
52179	52179	R 12V Charger		
52180	52180	R 230V Charger		

**DISTRIBUTED BY:**

- Designed specifically for cutting fine stranded copper cable.
- State of the art 18V lithium ion (Li-ion) battery provides 70% more cycles per charge and faster cycle times.
- LED light provides the operator with the battery charge and tool maintenance status.
- In line tool style is light weight and very easy to control.
- One trigger controls all tool functions.
- Cutting head rotates 350°.
- Tools automatically retract when the cutting cycle is complete.
- Overmolded tacky grip areas make gripping the tool easier and more comfortable.
- LED work light illuminates dark work areas.
- Greenlee battery-powered crimping tools now use bio-degradable oil.
- Smart chargers control the charging current, charging voltage and battery temperature to maximize battery life.
- Available with 120V, 12V or 230V battery charger or with 120V or 230V corded adapter in place of batteries and charger.

### SPECIFICATIONS

Capacity	1-1/4" (32 mm) fine stranded Copper cable (Not for cutting standard stranded cables)
Battery Voltage	18V 1.5 Ah Li-ion
Length	14-5/8" (372 mm)
Weight	4.4 lbs. (2.0 kg)
Battery Charge Time	Approximately 30 minutes
Est. Cycles Per Charge	200 (500kcmil cable requires 2 cycles per cut)

CAT. NO.	UPC NO.	DESCRIPTION	R = REPLACEMENT PART	A = ACCESSORY
ES32FL11	19219	ES32FL Battery-Powered Cable Cutter with 120 V Charger		
ES32FL12	19220	ES32FL Battery-Powered Cable Cutter with 12 V Charger		
ES32FL22	19221	ES32FL Battery-Powered Cable Cutter with 230 V Charger		
ES32FL120	19222	ES32FL Battery-Powered Cable Cutter with 120 V Charger		
ES32FL230	19223	ES32FL Battery-Powered Cable Cutter with 230 V Charger		
19234	19234	R Blade Kit		
52177	52177	R 18V 1.5 Ah Li-ion		
25752	25752	R Carrying Case		
52178	52178	R 120V Charger		
52179	52179	R 12V Charger		
52180	52180	R 230V Charger		

**GREENLEE®**  
A Textron Company

[www.greenlee.com](http://www.greenlee.com) • MA-5537 09/2010  
4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070  
©2010 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA  
Greenlee Textron Inc. is a subsidiary of Textron Inc.



USA

Tel: 800.435.0786  
Fax: 800.451.2632

CANADA

Tel: 800.435.0786  
Fax: 800.524.2853

INTERNATIONAL

Tel: +1.815.397.7070  
Fax: +1.815.397.9247