

# ES GL840ES-2442 SERIES



Shown with optional accessories,  
drawings can be found on page 136

**DIMENSIONS:** 84"H x 24"W x 42"D

Maximum rail placement: 35"; Usable inside depth: 40"  
9" of dedicated cable management/PDU depth in rear

**RACK SPACES:** 44 RMU • 19" EIA 310-D Compliant

**STOCK COLORS:** Black or Advantage White

**WEIGHT CAPACITY:**

2000 lbs. on levelers or bolted to floor; 1800 lbs. on casters

**SHIPPING WEIGHT AND PALLET SIZE:**

425 lbs./90"H x 32"W x 45"D

## **GL840ES-2442MS COMPLETE ENCLOSURE INCLUDES PARTS BELOW**

<b>PART NO.</b>	<b>DESCRIPTION</b>
8401ES-2442	Frame with two pairs of black powder coated, universal 19" M6 mounting rails (with RMU markings) and package of M6 hardware; includes two pairs of PDU mounting brackets with three holes each
7209-N	One Set of 4 Adjustable Levelers (2.5"H)
TPES-S	Solid Top Panel
8402E-MC24	Front Contour Mesh Door with locking handle
8402E-MC24	Rear Contour Mesh Door with locking handle
8410-36ELS	Pair of Solid Lift-off Side Panels with lock and finger release latches

## **ADDITIONAL CONFIGURATIONS**

GL840ES-2442MSS	Complete enclosure with Contour Mesh Front Door and Split Mesh Rear Door
GL840ES-2442MSFS	Complete enclosure with Contour Mesh Front Door and Split Fan Rear Door
GL840ES-2442LC	Localized Containment Kit: Complete enclosure with Contour Mesh Front Door, Solid Rear Door, Air Manager, Air Manager Fan Tray (600 CFM), Exhaust Chimney with an 18" to 32" adjustable range, Chimney Fan Tray (1200 CFM), and Brush Grommet Kit

