

EN GL840EN-3242 SERIES



DIMENSIONS: 84"H x 32"W x 42"D

RACK SPACES: 45 RMU • 19" EIA 310-D Compliant

STOCK COLOR: Black

WEIGHT CAPACITY:

2000 lbs. on levelers or bolted to floor

SHIPPING WEIGHT AND PALLET SIZE:

350 lbs./ 90"H x 35"W x 45"D

PART NO.

GL840ENT-3242MSS

DESCRIPTION

Enclosure with two pair of tapped #12-24 mounting rails with cable management fingers on all rails; includes solid top, mesh front door, split mesh rear door, and solid sides

GL840ENT-3242MSS-NS

Enclosure with two pair of tapped #12-24 mounting rails with cable management fingers on all rails; includes solid top, mesh front door, split mesh rear door; sides not included

GL840ENT-3242-FK

Enclosure with two pair of tapped #12-24 mounting rails with cable management fingers on all rails; doors and sides not included

For enclosure with M6 rails, remove 'T' from part number.

ACCESSORIES

PART NO.

ENT-S

ENC-K24

8402EN-M32

8402EN-32SM

8410421-ENLS

CBB-72

GR101

TCT32

LRB-12

DESCRIPTION

Solid Top Panel

Cable Management Rail Kit; includes 24 sections of "fingers" (each section 7 RMU)

Mesh Door assembly for 32"W

EN Enclosure

Split Mesh Door assembly for 32"W

EN Enclosure

Solid side panel for 42"D EN Enclosure

Copper Bus Bar, 70" (isolated)

Grounding Kit

Top Cable Trough

Ladder Rack Bracket for 12"W ladder rack; includes hardware

Shown with optional accessories,
drawings can be found on page 137

