

GL840EN-4048 SERIES EN



DIMENSIONS: 84"H x 40"W x 48"D

RACK SPACES: 45 RMU • 19" EIA 310-D Compliant

STOCK COLOR: Black

WEIGHT CAPACITY:

2000 lbs. on levelers or bolted to floor

SHIPPING WEIGHT AND PALLET SIZE:

450 lbs./ 90"H x 43"W x 51"D

PART NO.

GL840ENT-4048SSS

DESCRIPTION

Enclosure with two pair of tapped #12-24 mounting rails with cable management fingers on all rails; includes solid top, split mesh front door, split mesh rear door, solid sides, and baffle kit (25 RMU) for CISCO® 7018 switch

GL840ENT-4048SSS-NS

Enclosure with two pair of tapped #12-24 mounting rails with cable management fingers on all rails; includes solid top, split mesh front door, split mesh rear door, and baffle kit (25 RMU) for CISCO® 7018 switch; sides not included

GL840ENT-4048-FK

Enclosure with two pair of tapped #12-24 mounting rails with cable management fingers on all rails; includes baffle kit (25 RMU) for CISCO® 7018 switch; doors and sides not included

For enclosure with M6 rails, remove 'T' from part number.

ACCESSORIES

PART NO.

ENT-S

ENC-K24

8402EN-40SM

8410481-ENLS

CBB-72

GR101

TCT40

LRB-12

DESCRIPTION

Solid Top Panel

Cable Management Rail Kit; includes 24 sections of "fingers" (each section 7 RMU)
Split Mesh Door assembly for 40"W
EN Enclosure

Solid side panel for 48"D EN Enclosure
Copper Bus Bar, 70" (isolated)

Grounding Kit

Top Cable Trough

Ladder Rack Bracket for 12"W ladder rack; includes hardware



Drawings can be found on page 137