

E GL840E-2436 SERIES



DIMENSIONS: 84"H x 24"W x 36"D

Maximum rail placement and usable inside depth: 34"

RACK SPACES: 44 RMU • 19" EIA 310-D Compliant

STOCK COLORS: Black, Advantage White, or Nitro Blue

WEIGHT CAPACITY:

1500 lbs. on levelers, bolted to floor, or on heavy duty casters

SHIPPING WEIGHT AND PALLET SIZE:

350 lbs./90"H x 32"W x 38"D

GL840E-2436P COMPLETE ENCLOSURE INCLUDES PARTS BELOW

PART NO.	DESCRIPTION
8401E-2436	Frame with two pairs of black powder coated, universal 19" M6 mounting rails (with RMU markings) and package of M6 hardware
7209-N	One Set of 4 Adjustable Levelers (2.5"H)
TPE-24P	Removable Vented Top Panel with two 4" horseshoe knockouts
8402E-24	Plexiglas Front Door with locking swing handle
8404E-24	Perimeter Vented Steel Rear Door with locking swing handle
8410-36ELS	Pair of Solid Lift-off Side Panels with lock and finger release latches
7215	16 position, 15 amp Power Strip; 5-15R receptacle and 5-15P plug

ADDITIONAL CONFIGURATIONS

GL840E-2436F	Complete enclosure with TPE-24F (top panel with three 75 CFM fans)
GL840E-2436F10	Complete enclosure with TPE-24F10 (top panel with one 10", 550 CFM fan)
GL840E-2436MP	Complete enclosure with mesh front & rear doors and TPE-24P vented top
GL840E-2436MCP	Complete enclosure with mesh front door, mesh contour rear door and TPE-24P vented top
GL840E-2436MSP	Complete enclosure with mesh front door, split mesh rear door and TPE-24P vented top (available in black only)

Shown with optional accessories,
drawings can be found on page 138