

E GL720E-2936 SERIES



DIMENSIONS: 72"H x 29"W x 36"D

Maximum rail placement and usable inside depth: 34"

RACK SPACES: 37 RMU • 19" EIA 310-D Compliant

STOCK COLORS: Black, Advantage White, or Nitro Blue

WEIGHT CAPACITY:

1500 lbs. on levelers, bolted to floor, or on heavy duty casters

SHIPPING WEIGHT AND PALLET SIZE:

350 lbs./78"H x 32"W x 38"D

GL720E-2936P COMPLETE ENCLOSURE INCLUDES PARTS BELOW

PART NO.	DESCRIPTION
7201E-2936	Frame with two pairs of black powder coated, universal 19" M6 mounting rails (with RMU markings) and package of M6 hardware
7209-N	One Set of 4 Adjustable Levelers (2.5"H)
TPE-29P	Removable Vented Top Panel With two 4" horseshoe knockouts
7202E-29	Plexiglas Front Door with locking swing handle
7204E-29	Perimeter Vented Steel Rear Door with locking swing handle
7210-36ELS	Pair of Solid Lift-off Side Panels with lock and finger release latches
7215	16 position, 15 amp Power Strip; 5-15R receptacle and 5-15P plug

ADDITIONAL CONFIGURATIONS

GL720E-2936F	Complete enclosure with TPE-29F (top panel with three 75 CFM fans)
GL720E-2936F10	Complete enclosure with TPE-29F10 (top panel with one 10", 550 CFM fan)
GL720E-2936S	Complete enclosure with TPE-29S solid top

Shown with optional accessories,
drawings can be found on page 138

