

E GL720E-2932 SERIES



DIMENSIONS: 72"H x 29"W x 32"D

Maximum rail placement and usable inside depth: 30"

RACK SPACES: 37 RMU • 19" EIA 310-D Compliant

STOCK COLORS: Black, Advantage White, or Nitro Blue

WEIGHT CAPACITY:

1500 lbs. on levelers, bolted to floor, or on heavy duty casters

SHIPPING WEIGHT AND PALLET SIZE:

350 lbs./78"H x 32"W x 38"D

GL720E-2932P COMPLETE ENCLOSURE INCLUDES PARTS BELOW

PART NO.

7201E-2932

DESCRIPTION

Frame with two pairs of black powder coated, universal 19" M6 mounting rails (with RMU markings) and package of M6 hardware

7209-N

One Set of 4 Adjustable Levelers (2.5"H)

TPE-29P

Removable Vented Top Panel With two 4" horseshoe knockouts

7202E-29

Plexiglas Front Door with locking swing handle

7204E-29

Perimeter Vented Steel Rear Door with locking swing handle

7210-32ELS

Pair of Solid Lift-off Side Panels with lock and finger release latches

7215

16 position, 15 amp Power Strip; 5-15R receptacle and 5-15P plug

ADDITIONAL CONFIGURATIONS

GL720E-2932F Complete enclosure with TPE-29F (top panel with three 75 CFM fans)

GL720E-2932F10 Complete enclosure with TPE-29F10 (top panel with one 10", 550 CFM fan)

GL720E-2932S Complete enclosure with TPE-29S solid top

Shown with optional accessories,
drawings can be found on page 138

