

E GL480E-2432 SERIES



DIMENSIONS: 48"H x 24"W x 32"D
Maximum rail placement and usable inside depth: 30"

RACK SPACES: 24 RMU • 19" EIA 310-D Compliant

STOCK COLORS: Black, Advantage White, or Nitro Blue

WEIGHT CAPACITY: 600 lbs.

SHIPPING WEIGHT AND PALLET SIZE:
210 lbs./54"H x 32"W x 38"D

GL480E-2432P COMPLETE ENCLOSURE INCLUDES PARTS BELOW

PART NO.	DESCRIPTION
4801E-2432	Frame with two pairs of black powder coated, universal 19" M6 mounting rails (with RMU markings) and package of M6 hardware
7209-N	One Set of 4 Adjustable Levelers (2.5"H)
TPE-24P	Removable Vented Top Panel with two 4" horseshoe knockouts
4802E-24	Plexiglas Front Door with locking swing handle
4804E-24	Perimeter Vented Steel Rear Door with locking swing handle
4810-32ELS	Pair of Solid Lift-off Side Panels with lock and finger release latches
7218-24	8 position, 15 amp Power Strip; 5-15R receptacle and 5-15P plug

ADDITIONAL CONFIGURATIONS

GL480E-2432F	Complete enclosure with TPE-24F (top panel with three 75 CFM fans)
GL480E-2432F10	Complete enclosure with TPE-24F10 (top panel with one 10", 550 CFM fan)
GL480E-2432S	Complete enclosure with TPE-24S solid top

Shown with optional accessories,
drawings can be found on page 138

