

# E GL300E-2432 SERIES



Drawings can be found on page 138



**DIMENSIONS:** 30"H x 24"W x 32"D

Maximum rail placement and usable inside depth: 30"

**RACK SPACES:** 13 RMU • 19" EIA 310-D Compliant

**STOCK COLORS:** Black, Advantage White, or Nitro Blue

**WEIGHT CAPACITY:** 300 lbs

**SHIPPING WEIGHT AND PALLET SIZE:**

160 lbs./36"H x 32"W x 38"D

## GL300E-2432P COMPLETE ENCLOSURE INCLUDES PARTS BELOW

PART NO.	DESCRIPTION
3001E-2432	Frame with two pairs of black powder coated, universal 19" M6 mounting rails (with RMU markings) and package of M6 hardware
7209-N	One Set of 4 Adjustable Levelers (2.5"H)
TPE-24P	Removable Vented Top Panel with two 4" horseshoe knockouts
3002E-24	Plexiglas Front Door with locking swing handle
3004E-24	Perimeter Vented Steel Rear Door with locking swing handle
3010-32ELS	Pair of Solid Lift-off Side Panels with lock and finger release latches
7219	6 position, Power Strip; 5-15R receptacle and 5-15P plug

## ADDITIONAL CONFIGURATIONS

GL300E-2432F	Complete enclosure with TPE-24F (top panel with three 75 CFM fans)
GL300E-2432F10	Complete enclosure with TPE-24F10 (top panel with one 10", 550 CFM fan)
GL300E-2432S	Complete enclosure with TPE-24FS solid top