

CO-LO ENCLOSURE CL



The Co-Lo provides separate entry for each compartment; approved personnel are able to access the necessary equipment, while the remaining equipment is protected from unauthorized use.

- Pre-assembled to your equipment configuration
- Secure vertical cable management raceways
- Cable access provisions located on top and bottom
- Grounding studs on doors, side panels, and base unit
- Fan assembly located on each rear door optional

DIMENSIONS: 84"H x 28"W x 36"D

Maximum rail placement and usable inside depth: 34"

RACK SPACES: 21 RMU per compartment • 19" EIA 310-D Compliant

STOCK COLOR: Black

WEIGHT CAPACITY: 1500 lbs. on levelers or bolted to floor

SHIPPING WEIGHT AND PALLET SIZE:

500 lbs./90"H x 32"W x 38"D

PART NO.

DESCRIPTION

GL84CL2MM

Complete 2 compartment Co-Lo Cabinet (21 RMU per compartment) with mesh front and rear doors; secure vertical cable management raceways (44.38"H x 5.75"W x 2.75"D)

GL84CL2PF

Same as GL84CL2MM except with perimeter vented plexi front doors and solid rear doors with built in exhaust fans

ACCESSORIES

PART NO.

DESCRIPTION

7219

6 position Power Strip for 19" mounting; 5-15R receptacle and 5-15P plug

7219-20AR

6 position, 20 amp Power Strip for 19" mounting; 5-20R receptacle and 5-20P plug

7206-FR-AHD

Stationary Shelf, front/rear mount adjustable, 17.5"W x 22.25"D,

200 lb. weight capacity

CM-04

Interbay Cable Organizer with 4 front horizontal rings, 3.25"W x 2.8"D

CBB-19

Copper Bus Bar for 19" mounting (isolated)

GR101

Grounding Kit

AK101

Seismic Anchor Kit (includes 4 torque controlled expansion anchors)

7208-E

One Set of 4 Casters, 2 locking and 2 non-locking

7209-N

One Set of 4 Adjustable Levelers (2.5"H)

CH-02

Door Handle with three digit combination and key



Shown with optional accessories