



Shown with optional accessories

## FEATURES

- 19" EIA 310-D Compliant
- Side mounting reduces the open space required to mount equipment; mounting across 3 studs provides extra stability
- 2 pair of M6 rails; fully adjustable
- 1, 2, and 3" conduit knockouts on top and bottom
- 1, 2, and 3" conduit knockouts on rear of wall mount

## WE SERIES PART NO.

PART NO.	DESCRIPTION
GL24WE	24"H x 36.1"W x 20.5"D, Usable space 34", Maximum rail spacing 29", 10 RMU, Wt. cap. 350 lbs., Shipping wt. 100 lbs., Mesh side doors and solid front panel; includes M6 cage nuts

## ACCESSORIES

PART NO.	DESCRIPTION
7219	6 position Power Strip for 19" mounting; 5-15R receptacle and 5-15P plug
7219-SR14	14 position (6 front/8 back) Power Strip for 19" mounting; 5-15R receptacle and 5-15P plug with surge protector
7217WS	Fan Assembly with fan guards and two 75 CFM fans



Shown with optional accessories

## FEATURES

- 19" EIA 310-D Compliant
- Ideal for switches and sound equipment when space is limited
- #10-32 mounting holes and three position adjustable rails
- Removable cover allows for left, right, or vertical equipment orientation

## WR SERIES PART NO.

PART NO.	DESCRIPTION
WR2	4"H x 19.75"W x 21.63"D, Usable space 21", Rack spaces: 2 RMU, Wt. cap. 50 lbs., Shipping wt. 17 lbs.
WR4	7.5"H x 19.75"W x 21.63"D, Usable space 21", Rack spaces: 4 RMU, Wt. cap. 75 lbs., Shipping wt. 20 lbs.