

# W SRD, SR



## FEATURES

- 19" EIA 310-D Compliant
- #12-24 mounting holes
- Deeper than traditional swing racks
- Easy to assemble, install and mount

## SRD SERIES SWING RACK (DEEP)

PART NO.	DESCRIPTION
GL24SRD	24"H x 20.75"W x 24"D, Usable depth 22", 12 RMU, Wt. cap. 100 lbs., Shipping wt. 34 lbs., includes #12-24 screws
GL36SRD	36.25"H x 20.75"W x 24"D, Usable depth 22", 19 RMU, Wt. cap. 100 lbs., Shipping wt. 44 lbs., includes #12-24 screws
GL48SRD	48.5"H x 20.75"W x 24"D, Usable depth 22", 26 RMU, Wt. cap. 100 lbs., Shipping wt. 54 lbs., includes #12-24 screws



## FEATURES

- 19" EIA 310-D Compliant
- #12-24 mounting holes
- 180° positive stop with stay open hinge pins
- Easy to assemble, install and mount

## SR SERIES SWING RACK

PART NO.	DESCRIPTION
GL24SR	23.75"H x 20.75"W x 18"D, Usable depth 16", 12 RMU, Wt. cap. 100 lbs., Shipping wt. 30 lbs., includes #12-24 screws
GL36SR	36"H x 20.75"W x 18"D, Usable depth 16", 19 RMU, Wt. cap. 100 lbs., Shipping wt. 36 lbs., includes #12-24 screws
GL48SR	48.75"H x 20.75"W x 18"D, Usable depth 16", 26 RMU, Wt. cap. 100 lbs., Shipping wt. 48 lbs., includes #12-24 screws