

R 4 POST RACKS



DIMENSIONS: 84"H x 20.6"W, Rail Depth Ranges from 24" to 36"

RACK SPACES: 45 RMU • 19" EIA 310-D Compliant

WEIGHT CAPACITY: 1500 lbs. when networked; 1000 lbs. free standing

CONSTRUCTION: 12 Gauge Cold Rolled Steel and Extruded Aluminum

SHIPPING WEIGHT: Please see Part No. Description

PART NO.	DESCRIPTION
4PM6-29-5FO	29"D Rack with M6 Mounting and 5" Vertical Front Cable Management; cold rolled steel construction; includes mounting hardware
4PM6-29-5FR	Same as above except with 5" Vertical Front and Rear Cable Management
4PM6-29-8FO	Same as above except with 8" Vertical Front Cable Management (includes cover)
4PM6-29-8FR	Same as above except with 8" Vertical Front and Rear Cable Management (includes cover)
4PM6-24	24"D Rack with M6 Mounting; cold rolled steel construction includes mounting hardware; 3 cartons totaling 82 lbs.
4PM6-29	Same as above except with 29"D; 3 cartons totaling 83 lbs.
4PM6-32	Same as above except with 32"D; 3 cartons totaling 86 lbs.
4PM6-36	Same as above except with 36"D; 3 cartons totaling 87 lbs.
4P1224-24	24"D Rack with #12-24 Mounting; aluminum upright construction and steel bracket set; includes mounting hardware; 3 cartons/64 lbs.
4P1224-29	Same as above except with 29"D; 3 cartons totaling 65 lbs.
4P1224-32	Same as above except with 32"D; 3 cartons totaling 68 lbs.
4P1224-36	Same as above except with 36"D; 3 cartons totaling 69 lbs.

ACCESSORIES

PART NO.	DESCRIPTION
7215-20ARTLP	16 position Power Strip; 5-20R receptacle and L5-20P plug; requires PSBGLRR
PSBGLRR	Vertical Power Strip Mounting Brackets
7206-FR-A32HD	Stationary Shelf (front/rear mount adjustable) 17.5"W x 32"D, 300 lb. weight capacity
7206-FRSL-ADHD	Sliding Shelf (front/rear mount adjustable) 17.5"W x 26"D, 110 lb. weight capacity
GL-RMUTA	Package of 4 RMU Labels in ascending order (1 on the bottom, 45 on the top)



Shown with optional accessories