

# FutureCom™ E Patch Cord, FRNC, RJ45 - RJ45 connector

black / blue, 3 m

CORNING

The black FutureCom™ Cat.6 patch cords with 2x RJ45 plugs in compliance with IEC 60603-7-5 Ed.1.0 provide transmission performance according to Category 6 specifications of ISO/IEC 11801 Edition 2.2 and EN 50173 (series).

FutureCom cables are low skew products, i.e. the difference in propagation delay between the individual pairs is very low, an increasing requirement for Gigabit Ethernet. The suitability of the cable for high-bit-rate transmission systems ensures a high degree of future proofing throughout the system.

The RJ45 connectors are fully assigned and hence application independent. Additional features are the slim design and low weight of the flex cables. Each pair is individually shielded with foil (FTP). FutureCom™ Cat.6 patch cords provide additional latch protection through the different coloured boot options available.

## Features

- RJ45 to RJ45 according to IEC 60603-7-5 (2010-04) Ed. 2.0
- Application independent, all four pairs terminated
- Halogen-free (LS0H/LSZH), flame-retardant
- Coloured latch protection
- Supports Gigabit Ethernet
- Category 6 component



Part Number: CCAEIA-DQ002-A030-C0



Part Number: CCAEIA-DQ002-A030-C0

# FutureCom™ E Patch Cord, FRNC, RJ45 - RJ45 connector

black / blue, 3 m

CORNING

## Specifications

### General Specifications

Cable Assembly Type	Patch Cords
Environment	Indoor
Cable Type	U/FTP
Halogen-free	Yes
Category	6

### Design - Connector A

Connector Type	RJ45 - 8/8
----------------	------------

### Mechanical Specifications - Connector A

Durability	750 Cycles
------------	------------

### Electrical Specifications - Connector

Insulation Resistance	> 5000 MΩ
-----------------------	-----------

### Design - Connector B

Copper Connector Type - B	RJ45 - 8/8
---------------------------	------------

### Cable Design

Outer diameter	5.5 mm
Min. Bend Radius Installation	40 mm
Min. Bend Radius Operation	30 mm
No. of Pairs	4
Outer Jacket Material	LSZH™/FRNC
Outer Jacket Colour	Black

# FutureCom™ E Patch Cord, FRNC, RJ45 - RJ45 connector

black / blue, 3 m

CORNING

## Mechanical Characteristics

Conductor insulation	Foam Skin PE
Copper conductor	AWG26
Operating temperature	-20 °C to 60 °C

## Chemical characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

## Ordering Information

Part Number	CCAIEA-DQ002-A030-C0
Product Description	FutureCom™ E Patch Cord, FRNC, RJ45 - RJ45 connector, cable black, boot blue, 3 m
Colour	Black / Blue
Weight	0.15 kg
Length	3 m

## Shipping Information

Units per Delivery	1/1
--------------------	-----



Corning Cable Systems GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, GERMANY  
00 800 2676 4641 · FAX: +49 30 5303 2335 · [www.corning.com/cablesystems/emea](http://www.corning.com/cablesystems/emea)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/emea/trademarks](http://www.corning.com/cablesystems/emea/trademarks). Corning Cable Systems is ISO 9001 certified. © 2014 Corning Cable Systems. All rights reserved.