

Miniature Weather/Vandal Resistant Color Cameras with IR LEDs

CVC71HRB CVC71HRW

3.4mm fixed lens, black housing

3.4mm fixed lens, white housing

Features

- 1/3" Sony Super-HAD™ CCD
- 540 TV lines resolution
- Built-In 3.4mm fixed lens
- 10 IR LEDs built-in
- Compact size - Only 1.89" in diameter!
- Vandal resistant housing
- Cast aluminum construction
- Impressive picture quality
- IP66 compliant
- Perfect for use in vehicles
- 5 year warranty

Specifications

Image Sensor	1/3" Sony Super-HAD™ CCD
Resolution.....	540 TV lines
Minimum Illumination.....	0.1 lux (IR LEDs off) 0.0002 lux (IR LEDs on)
Effective Pixels	768 (H) x 594 (V)
IR LEDs	10 Built-In
IR Range	30'
White Balance	Auto
Gain Control	Auto
S/N Ratio	More than 50dB (AGC Off)
Video Output.....	1.0Vp-p - 75 Ohm
Electronic Shutter Speed.....	Auto: 1/60 sec. - 1/120,000 sec.
Scanning Frequency.....	15.734KHz (H) / 60Hz (V)
Scanning System.....	2:1 interlaced
Synchronization	Internal
Power Consumption	120mA Max.
Power Supply	12VDC (power supply not included)
Operating Temperature.....	-14° F - 120° F
Dimensions.....	1.46" (H) x 1.89" (Dia)
Weight	4 oz.



Optional Accessories



Speco Technologies is constantly developing and improving products.
We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 12/7/12

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com