

VM10LCD

Features

- Professional TFT LCD for surveillance with multiple connections
- Picture-In-Picture feature that allows multi-picture display (in VGA mode)
- High brightness level and contrast ratio with super wide viewing angle
- Built-in 3D comb filter and 3D de-interlace for display picture performance
- Fast response time and refresh rate

Specifications

- Panel Size..... 10.4"
- Aspect Ratio..... 4:3
- Resolution/Scan..... 640 x 480
- Brightness..... 350 cd/m2
- Contract Ratio..... 300:1
- Viewing Angle (H/V)..... Left 70° / Right 70° / Up 40° / Down70°
- Response Time..... 6ms (Typ.)
- Sync. Format..... NTSC / PAL
- Frequency (Horizontal)..... PC: 31.5K
- Frequency (Vertical)..... PC: 60Hz - 75Hz, Video: 50 / 60Hz
- Video Interface..... D-SUB 15IN x 1, Video In x 2 (BNC), Video Out x 2 (BNC), S-Video In x 1
- Audio Interface..... In x 2, Audio Out x 2, PC-Audio In x 1
- Input Power..... DC In x 1
- Termination..... 75 Ohm (AutoTermination)
- Built-In Speakers..... Yes (2pcs)
- Front Panel Button..... Power, Source, Up, Down, Menu, Auto
- OSD Language..... Multi Language
- VESA Mounting..... VESA 75mm x 75mm
- Power Supply..... 12VDC
- Power Consumption (max.)..... 17.2W
- Operating Temperature/
Humidity..... 14° F - 122° F / RH 20% - 80%
- Dimensions..... 10.3" (W) x 8.8" (H) x 2.5" (D)
- Weight (N.W. / G.W.)..... 4 lbs. / 6.4 lbs.
- Included in Package..... Power cord, user manual, remote control

