

OD101

Features

OD101 is a standalone dual-codec (H.264 & MJPEG) decoder with audio for IP cameras and video servers. It restores CVBS analog video and audio from IP video streams received from IP cameras or video servers.

IP addresses of up to 32 IP video sources can be stored for sequential connection with independent dwell time.

- Dual-codec (H.264 & MJPEG)
- Small footprint, low power
- IP video, ADPCM audio
- CVBS and audio output
- Automatic reconnection in case of network failure
- 2 year warranty

Video Specifications

Video Compression	Simultaneous dual-codec (H.264 / MJPEG)
Resolution.....	720x480 (full D1), 720x240 (half D1), 352x240 (CIF), 176x144 (QCIF)
Video Input	32 ch. IP
Video Output.....	1 ch. CVBS

Audio Specifications

Mono Upstream.....	64Kbps 16-bit linear PCM
Mono Downstream	32Kbps G.726 ADPCM

Network Specifications

Access Network.....	100Base-T, xDSLModem, cable modem, leased line, optic fiber
Protocols.....	IPv4, TCP/IP, ARP, DHCP, RTSP
Security.....	User ID & password protection
Dynamic IP	Supported



External Terminals

LAN.....	10/100BaseT LAN (auto MDIX)
RS-485	RS-485 for external PTZ device
Alarm Output	N/A
Factory Reset	Supported

Client Software

Decoder finder	OnSIP installer & admin tool (IE)
----------------------	-----------------------------------

Operating Environment, Power, Dimensions

Operating Temperature/	
Humidity.....	32° F – 122° F / 8% – 80% RH
Power Supply	12VDC, 0.4mA (power supply not included)
Power Consumption	0.4mA
Dimensions.....	3" (W) x 1" (H) x 4" (L)
Weight	6.72 oz.
Approvals.....	FCC, CE, MIC, RoHS

Optional Accessory



PSW5
12VDC
Power Supply

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.



Rev. 4/19/13

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com