

Seven Zone 260 Watt Commercial Amplifier

PL260A 260W commercial amplifier

Features

Our Platinum 260 model (PL260A) delivers 260 watts of RMS power while featuring seven 25 or 70 volt paging zones. A 24 Volt battery backup input terminal delivers reassurance in the event of a power failure, safeguarding that internal communications can still be maintained. Five XLR microphone connectors with individual phantom power switches, and three auxiliary jacks deliver ample inputs that will cover most any end user needs.

Additional features of music-on-hold, a 600 Ohms telephone paging input, pre-amp input, booster output, 4/8/16 Ohm speaker outputs, an auxiliary output and separate bass and treble controls. Ideal for schools, offices, manufacturing and more.

- Pre amp input/booster output
- Additional auxiliary output
- Music-on-hold feature
- Separate bass and treble controls

Specifications

RMS Power: 260W

Seven 70/25V zone outputs with 70/25V selector switch

24 volt Input for emergency back up power

5 XLR MIC connector inputs with phantom power switches

3 AUX inputs

4/8/16 Ohms output, non-zoned

1 telephone paging input (0.1-1V 600 Ohms)

AC 117V/60Hz

Seven zone On/Off selectors on face plate

Dimensions: 16.9" (W) x 3.5" (H) x 11.6" (D)

Rack mounting kit available: **PBMRK2**



rear of unit

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 4/18/12

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com