

AWX Series All-Weather Extreme Indoor/Outdoor Speakers

SP5AWX	5.25" Black - Sold in pairs
SP5AWXW	5.25" White - Sold in pairs
SP6AWX	6.5" Black - Sold in pairs
SP6AWXW	6.5" White - Sold in pairs
SP5AWXT	5.25" Black with transformer - Sold in pairs
SP5AWXTW	5.25" White with transformer - Sold in pairs
SP6AWXT	6.5" Black with transformer - Sold in pairs
SP6AWXTW	6.5" White with transformer - Sold in pairs

Features

- Great aesthetics and superb sound at a great price point.
- Designed with premium specifications and stylishly cut cabinets, these weather resistant speakers deliver the performance and quality our customers have come to expect from Speco Technologies.
- Extreme Performance In Extreme Weather For An Extremely Affordable Price. Thats The New AWX Series.

Specifications



(Shown with Grille)

	SP5AWX SP5AWXW	SP6AWX SP6AWXW	SP5AWXT SP6AWXTW	SP6AWXT SP6AWXTW
Woofer	5.25" Polypropylene with Rubber Surround	6.5" Polypropylene with Rubber Surround	5.25" Polypropylene with Rubber Surround	6.5" Polypropylene with Rubber Surround
Tweeter	.75" Silk Dome Tweeter	1" Silk Dome Tweeter	.75" Silk Dome Tweeter	1" Silk Dome Tweeter
Frequency	75Hz-20kHz	60Hz-20kHz	75Hz-20kHz	60Hz-20kHz
Sensitivity	88 dB 1 w/1m	90 dB 1 w/1m	88 dB 1 w/1m	90 dB 1 w/1m
Wattage	40 Watts RMS / 80 Watts Max.	50 Watts RMS / 100 Watts Max.	40 Watts RMS / 80 Watts Max.	50 Watts RMS / 100 Watts Max.
Dimensions	9" H x 6" W x 6 1/4" D	11" H x 7" W x 6 3/4" D	9" H x 6" W x 6 1/4" D	11" H x 7" W x 6 3/4" D
Weight	4.35 lbs. each	5.5 lbs. each	5.3 lbs. each	6.6 lbs. each
Impedance	8 Ohm	8 Ohm	8 Ohm	8 Ohm
Transformer	N/A	N/A	70V (40W, 20W, 10W, 5W, 2.5W & 8 Ohm)	70V (50W, 25W, 12.5W, 6W, 3W, & 8 Ohm)

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 9/19/11

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com