

MODULE	1000Base-SX LC SFP Module	1000Base-LX LC SFP Module	2.5 Gigabit SFP Module	2.5 Gigabit SFP Module	SFP Interconnect Cable (1m)	SFP Interconnect Cable (3m)	1000BaseT SFP Module
Description	Small Formfactor Pluggable (SFP) module providing a 1000Base-SX Gigabit Ethernet interface for multimode fiber	Small Formfactor Pluggable (SFP) module providing a 1000Base-LX Gigabit Ethernet interface for single-mode fiber	Small Formfactor Pluggable (SFP) module providing a Gigabit Ethernet interface for multimode fiber supporting rates from 1 Gbps to 2.5 Gbps.	Small Formfactor Pluggable (SFP) module providing a Gigabit Ethernet interface for single-mode fiber supporting rates from 1 Gbps to 2.5 Gbps.	SFP interconnect cable supporting 1Gbps and 2.5Gbps , SFP/SFP (1 Meter). With the NetVanta 1200 series (1st Gen) and NetVanta 1534 (1st Gen), the cable only supports 1Gbps.	SFP interconnect cable supporting 1Gbps and 2.5Gbps , SFP/SFP (3 Meters). With NetVanta 1200 series (1st Gen) and NetVanta 1534 (1st Gen), only supports 1Gbps.	Small Formfactor Pluggable (SFP) module that supports 10/100/1000Base-T
NetVanta 1224STR	✓	✓					
NetVanta 1234	✓	✓	✓	✓	✓	✓	✓
NetVanta 1234P	✓	✓	✓	✓	✓	✓	✓
NetVanta 1238	✓	✓	✓	✓	✓	✓	✓
NetVanta 1238P	✓	✓	✓	✓	✓	✓	✓
NetVanta 1335	✓	✓			✓	✓	
NetVanta 1335P	✓	✓			✓	✓	
NetVanta 1534	✓	✓	✓	✓	✓	✓	✓
NetVanta 1534P	✓	✓	✓	✓	✓	✓	✓
NetVanta 1554	✓	✓	✓	✓	✓	✓	✓
NetVanta 1554P	✓	✓	✓	✓	✓	✓	✓
NetVanta 1544F	✓	✓	✓	✓	✓	✓	✓
NetVanta 1638 with ActivChassis	✓	✓	✓	✓	✓	✓	
NetVanta 1638P with ActivChassis	✓	✓	✓	✓	✓	✓	
NetVanta 4430	✓	✓					
NetVanta 6355	✓	✓			✓	✓	
NetVanta 7100	✓	✓			✓	✓	
NetVanta 1535P with ActivReach	✓	✓	✓	✓	✓	✓	✓

MODULE2	10GBase-SR SFP+ Module	10GBase-LR SFP+ Module	NetVanta Dual Stacking XIM with 0.5m stacking cable	NetVanta Dual Stacking XIM with 2m stacking cable	NetVanta Dual Stacking XIM with 5m stacking cable	NetVanta Dual SFP XIM	NetVanta Dual SFP+ XIM
Description	Small Formfactor Pluggable+ (SFP+) module providing a Gigabit Ethernet interface for multimode fiber supporting rates from 1 Gbps to 10 Gbps.	Small Formfactor Pluggable+ (SFP+) module providing a 10 Gigabit Ethernet interface for single mode fiber supporting rates from 1 Gbps to 10 Gbps.	Dual stacking XIM with bundled 0.5m stacking cable . Provides 16 Gbps (32 Gbps Bi-directional) between NetVanta 1600 Gigabit Ethernet Switches.	Dual stacking XIM with bundled 2m stacking cable . Provides 16 Gbps (32 Gbps Bi-directional) between NetVanta 1600 Gigabit Ethernet Switches.	Dual stacking XIM with bundled 5m stacking cable . Provides 16 Gbps (32 Gbps Bi-directional) between NetVanta 1600 Gigabit Ethernet Switches.	The NetVanta Dual SFP XIM provides two high-speed SFP compliant 1 or 2.5 Gigabit Ethernet Interfaces, up to 5 Gbps bi-directional	The NetVanta Dual SFP+ XIM provides two high-speed SFP+ compliant 1 or 10 Gigabit Ethernet Interfaces, up to 20 Gbps bi-directional
NetVanta 1224STR							
NetVanta 1234							
NetVanta 1234P							
NetVanta 1238							
NetVanta 1238P							
NetVanta 1335							
NetVanta 1335P							
NetVanta 1534							
NetVanta 1534P							
NetVanta 1554							
NetVanta 1554P							
NetVanta 1544F							
NetVanta 1638 with ActivChassis	✓	✓	✓	✓	✓	✓	✓
NetVanta 1638P with ActivChassis	✓	✓	✓	✓	✓	✓	✓
NetVanta 4430							
NetVanta 6355							
NetVanta 7100							
NetVanta 1535P with ActivReach							