

Super-Flex® Traveling Cable Type ETT/300V

STEEL CENTER - UL LISTED, CSA CERTIFIED, NEC/CEC COMPLIANT - LIFETIME WARRANTY

Power, signal, shielded pairs and coax



Part Number	Product Code	Number/Size of Conductors	Steel Core Dia. inches • mm	Max. Hang Length ¹ feet • meters	Cable Nom. OD inches • mm	Cable Net Weight lbs/kft • kg/km
18-X61-13	CSX 61	7 / 14 AWG 27 / 18 AWG 13 shielded pair / 20 AWG 1 coax / RG6/U	1/4 • 6.4	900 • 275	1.65 • 41.9	1373 • 2043
18-X62-13	CSX 62 SP ^{††}	12 / 14 AWG 29 / 18 AWG 10 shielded pair / 20 AWG 1 coax / RG6/U	5/32 • 4.0	525 • 160	1.59 • 40.4	1334 • 1985
18-X69-13	CSX 69	5 / 14 AWG 40 / 18 AWG 11 shielded pair / 20 AWG 2 RG6/U coax	1/4 • 6.4	900 • 275	1.57 • 39.9	1340 • 1994
18-175-13	CSX 75 O	20 / 14 AWG 38 / 18 AWG 8 shielded pair / 20 AWG 1 coax / RG6/U	1/4 • 6.4	900 • 275	1.58 • 40.1	1472 • 2190
18-875-13	CSX 75 T	8 / 14 AWG 54 / 18 AWG 6 shielded pair / 20 AWG 1 RG6/U coax	5/32 • 4.0	542 • 165	1.58 • 40.1	1290 • 1920
18-377-13	CSX 77	4 / 14 AWG 69 / 18 AWG 1 shielded pair / 20 AWG 2 coax / RG6/U	5/32 • 4.0	532 • 162	1.64 • 41.6	1315 • 1957
18-X77-13	CSX 77 S	4 / 14 AWG 60 / 18 AWG 6 shielded pair / 20 AWG 1 coax / RG6/U	1/4 • 6.4	900 • 275	1.52 • 38.6	1269 • 1888
18-X80-13	CSX 80 SP ^{††}	10 / 14 AWG 39 / 18 AWG 15 shielded pair / 20 AWG 1 RG6/U coax	1/4 • 6.4	900 • 275	1.64 • 41.7	1560 • 2321
18-083-13	CSX 83	20 / 14 AWG 35 / 18 AWG 13 shielded pair / 20 AWG 2 coax / RG6/U	1/4 • 6.4	900 • 275	1.92 • 48.8	1808 • 2690



Power, signal, shielded pairs and fiber optics



Part Number	Product Code	Number/Size of Conductors	Steel Core Dia. inches • mm	Max. Hang Length ¹ feet • meters	Cable Nom. OD inches • mm	Cable Net Weight lbs/kft • kg/km
18-005-16	CSF 5	3 / 14 AWG 2 optical fibers / 62.5 µm	5/32 • 4.0	900 • 275	0.87 • 22.1	370 • 550
18-061-16	CWSF 61	4 / 14 AWG 49 / 18 AWG 3 shielded pair / 20 AWG 2 optical fibers / 62.5 µm	5/32 • 4.0	622 • 190	1.36 • 34.5	1125 • 1674
18-062-16	CSF 62	7 / 14 AWG 27 / 18 AWG 13 shielded pair / 20 AWG 2 optical fibers / 62.5 µm	5/32 • 4.0	900 • 275	0.87 • 22.1	370 • 550

¹For longer hang length applications, call with your requirements.

^{††}"SP" denotes special color coding and/or conductor numbering

RG6/U is the standard coaxial cable used in CSX-series Super-Flex cables and the preferred cable for CCTV purposes.

RG11/U coax and multimode optical fiber are available as options. See page 4 for specifics on these cables.