
Item no.: 222-412
Product description: Compact splicing connector 2-conductor terminal block with operating levers max. continuous service temperature 85°C



Produkt kann von Bild abweichen / product may differ

Packing unit 1000 10*100 pieces

RoHS compliant

Product group	7 (Push Wire Conn.)
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 14 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®CONNECTION
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Wiring method	f
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	32 A
Weight	3.072 g
Color	grey
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	14.5 mm
Height	0.571 in

Width 12.4 mm
Width 0.488 in
Depth 20.5 mm

Depth
0.807 in Strip length from
9 mm Strip length to
10 mm Strip length
0.37 in
Country of Origin

Deutschland

Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
222-412	ABS	10-HN17750340X	450	32	0,5-4
222-412	cULus listed	E69654	600	20	28-12
222-412	ENEC15	DK140137-01	450	32	0,5-4
222-412	PSE	JET0695-43040-1001	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected