

Color Compact Board Camera

CVC521BC 3.6mm fixed lens - optional lenses available

Features

- 1/3" color Sony Super HAD™ II CCD
- 600 TV lines of resolution
- Miniature size board camera with fixed lens
- 5 year warranty



Specifications

Image Sensor	1/3" color Sony Super HAD™ II CCD
Resolution.....	600 TV lines
Effective Pixels	768 (H) x 494 (V)
Minimum Illumination.....	0.1 lux, F1.2
Electronic Shutter Speed.....	1/60 sec. - 1/100,000 sec.
Scanning Frequency.....	15.75kHz (H) / 60Hz (V)
Scanning System.....	2:1 interlace
White Balance	Auto
S/N Ratio	More than 48dB (AGC off)
Video Output.....	1.0Vp-p / 75 ohms
Output.....	BNC output, power - DC jack
Power Consumption	80mA
Power Supply	12VDC (UL & CSA listed power supply included)
Operating Temperature/ Humidity.....	14° F – 122° F / within 95% RH
Dimensions.....	1.26" (W) x 1.26" (H)
Weight	0.35 oz.

Optional Lenses

CVC521BC2.2.....	2.2mm	CVC521BC8.....	8mm
CVC521BC2.5.....	2.5mm	CVC521BC12.....	12mm
CVC521BC2.9.....	2.9mm	CVC521BC16.....	16mm
CVC521BC6.....	6mm		

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation.
Spec Rev. 2/25/13