

DSWFUSB

Features

- Wireless access point for viewing and configuration of Speco DVRs and NVRs
- Compatible with DS and NS series DVRs

Specifications

Standards	IEEE 802.11b/n/g
Interface Type.....	USB 2.0/1.1
Security.....	64/128bit WEP encryption WPA/WPA2 and WPA-PSK/WPA2-PSK encryptions WiFi protected setup (WPS)
Operating.....	FCC: 2412-2462MHz (Ch1-Ch11)
Frequency.....	ETSI: 2412-2472MHz (Ch1-Ch13)
RF Frequency.....	2412-2462MHz (North America) 2412-2472MHz (Europe) 2412-2484MHz (Japan)
RF Power.....	11n Mode: 13dBm 11g Mode: 15dBm 11b Mode: 18dBm
LED Status	Link Status Activity
Operating Temperature/ Humidity.....	32° F – 104° F / 10% – 85% RH
Storage Temperature/ Humidity.....	-4° F – 140° F / 5% – 90% RH
Supported OS.....	Windows 2000/XP/Vista/ 7, Linux, Android, MAC

