

Economy Weather Resistant BW Bullet Camera

CVC130R 3.6mm wide angle lens, black housing
optional lenses available

Features

- Includes mounting bracket
- Weather resistant operation
- 5 year warranty



Specifications

Image Sensor	1/3" BW CCD
Resolution.....	420 TV lines
Minimum Illumination.....	0.02 lux
Effective Pixels	512 (H) x 492 (V)
Scanning System.....	2:1 interlace
Synchronization	Internal
Video Output.....	1.0Vp-p / 75 ohms
S/N Ratio	More than 48dB
Electronic Shutter Speed.....	Auto: 1/60 sec. - 1/100,000 sec.
Scanning Frequency.....	15.75kHz (H) / 60Hz (V)
Outputs/Connections	BNC - video output, power - DC jack
Power Supply	12VDC (UL & CSA listed power supply included)
Power Consumption	110mA
Operating Temperature/	
Humidity.....	- 20°F – 120°F / within 95% RH
Dimensions.....	1" (Dia.) x 2" (L)
Weight	2.2 oz.
Housing	Black / Aluminum



Speco Technologies is constantly developing and improving products.
We reserve the right to modify product design and specifications without
notice and without incurring any obligation.
Spec Rev. 2/12/14

Optional Lenses

CVC130R2.5	2.5mm lens
CVC130R6	6mm lens
CVC130R8	8mm lens
CVC130R12	12mm lens