

CVC812PC 2.5mm lens, black housing

Features

- Weather resistant door mount camera - looks like a normal peep-hole
- Single hole installation - easy and quick implementation
- Good low light sensitivity
- Maintenance free
- 5 year warranty

Specifications

Image Sensor	1/3" Interline CCD
Resolution	350 TV lines
Minimum Illumination	1.0 lux
Angle of View	150° diagonal - ultra wide angle coverage
Video Output	1.0Vp-p / 75 Ohms
Electronic Shutter	Auto: 1/60 sec. - 1/100,000 sec.
Output Video	BNC, power - DC jack
Power Consumption	500mA
Operating Temperature/	
Humidity	14° F – 122° F / within 95% RH
Housing	Metal
Power Supply	12VDC (UL and CSA listed power supply included)
Dimensions.....	2.75" (L) x 1.625" (H)
Depth of Door Requirement	2.75" in depth
Cable Length	40"
Weight	3.6 oz.



Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 2/20/13

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com