

## 960H Ultra Wide Angle Color Bullet Camera

**CVC638170** 2.2mm lens, 170° angle of view, black housing

### Features

- 170° field of view allows you to see small areas like elevators, vestibules, and counting rooms without any loss of coverage.
- The ultra-wide angle lens will fully view these small spaces when properly installed and positioned
- 1/3" Sony Super HAD II™ color CCD
- 700 TV lines of resolution
- Miniature mounting bracket included
- 5 year warranty

**960H**



### Specifications

Image Sensor .....	1/3" Sony Super HAD II™ color CCD
Resolution.....	700 TV lines
Minimum Illumination.....	0.001 lux (sense-up on)
Effective Pixels .....	976 (H) x 494 (V)
Total Pixels .....	1020 (H) x 508 (V)
Electronic Shutter .....	Auto 1/60 sec. – 100,000 sec.
Scanning Frequency.....	15.75kHz (H) / 60Hz (V)
Scanning System.....	2:1 interlace
S/N Ratio .....	More than 52dB
Video Output.....	1.0Vp-p / 75 ohms
Power Consumption .....	115mA
Power Supply .....	12VDC (UL & CSA listed power supply included)
Operating Temperature/	
Humidity.....	14° F – 122° F / within 95% RH
Dimensions.....	1.5" (W) x 3.2" (Dia.)
Weight .....	6.53 oz.

Speco Technologies is constantly developing and improving products.  
We reserve the right to modify product design and specifications without notice  
and without incurring any obligation. Spec Rev. 2/17/14