

# DYMO®

# Rhino

# 6000

## Industrial Labeling Tool



## Introducing the labeling tool that gets it done fast

The new RHINO 6000 is an ideal labeling tool for datacomm, professional Audio/Video, security and electrical systems, as well as all types of labeling throughout commercial buildings, factories, warehouses, and even homes.

The RHINO 6000 Label Printer is the first printer in the RHINO product family to offer PC connectivity. The installer can either create labels before reaching the worksite by downloading files from any Windows-based software program or they can create or edit labels while when they reach the worksite.

### Rhino 6000 Features:

- 1 Intuitive Graphical Interface** - Create, edit and preview multiple labels on our largest backlit LCD
- 2 One-Touch, Power-Assisted Cutter** - Eliminate the fatigue of manual cutting and increase efficiency
- 3 Hot Keys** - Eliminate guesswork, complicated menus and enjoy fast and easy formatting of commonly-used label types
- 4 Symbols** - Over 100 pre-programmed industry symbols
- 5 Save Your Labels** - Customize over 1,000 labels with logos and symbols and recall them instantly
- 6 Quick-Charge Li-Ion** - Rechargeable Battery with on-screen battery life indicator
- 7 Library** - Over 150 pre-programmed industry terms and the ability to customize your own library of terms
- 8 Powerful Serialization** - Built-in wizards for simple and advanced serialization
- 9 Integrated Impact Bumpers** - Protects against harsh conditions while allowing easy access to label cartridge



#### PC Connectivity

**Free Windows® driver** available at [www.rhinolabeling.com](http://www.rhinolabeling.com) for printing from any Windows® program via USB interface.

Upgrade printer firmware when new features become available.

#### Works best with RHINO CONNECT™ Software\*(not included) to:

- Upload/download label files for in-the-field and on-demand printing.
- Insert customized graphics, logos, symbols and industry terms.

- Import data from any Windows® based program.
- Create labels using the integrated step-by-step wizard.
- Print labels directly from RHINO CONNECT™ Software.

SKU# 1734519

List Price: \$249.99

# Rhino Labels

## Applications



Flat Surfaces



Curved Surfaces



Cable

### Flexible nylon

1/2" (12mm) • 3/4" (19mm)

Part #	Description	Length
18488	White Flexible Nylon Tape 1/2" (12mm)	11.5'
18489	White Flexible Nylon Tape 3/4" (19mm)	11.5'
18490	White Flexible Nylon Tape 1/2" (12mm)	11.5'
18491	White Flexible Nylon Tape 3/4" (19mm)	11.5'

### Permanent Polyester

3/8" (9mm) • 1/2" (12mm) • 3/4" (19mm)

Part #	Description	Length
18482	White Perm Poly Tape 3/8" (9mm)	18'
18483	White Perm Poly Tape 1/2" (12mm)	18'
18484	White Perm Poly Tape 3/4" (19mm)	18'
18508	Clear Perm Poly Tape 3/8" (9mm)	18'
622289	Clear Perm Poly Tape 1/2" (12mm)	18'
622290	Clear Perm Poly Tape 3/4" (19mm)	18'
18485	Metallized Perm Poly Tape 3/8" (9mm)	18'
18486	Metallized Perm Poly Tape 1/2" (12mm)	18'
18487	Metallized Perm Poly Tape 3/4" (19mm)	18'

### Vinyl

3/8" (9mm) • 1/2" (12mm) • 3/4" (19mm)

Part #	Description	Length
18443	White Vinyl 3/8" (9mm)	18'
18444	White Vinyl 1/2" (12mm)	18'
18445	White Vinyl 3/4" (19mm)	18'
18431	Yellow Vinyl 3/8" (9mm)	18'
18432	Yellow Vinyl 1/2" (12mm)	18'
18433	Yellow Vinyl 3/4" (19mm)	18'
18434	Orange Vinyl 3/8" (9mm)	18'
18435	Orange Vinyl 1/2" (12mm)	18'
18436	Orange Vinyl 3/4" (19mm)	18'
18437	Red Vinyl 3/8" (9mm)	18'
18438	Red Vinyl 1/2" (12mm)	18'
18439	Red Vinyl 3/4" (19mm)	18'
18440	Green Vinyl 3/8" (9mm)	18'
18441	Green Vinyl 1/2" (12mm)	18'
18442	Green Vinyl 3/8" (19mm)	18'

### Heat Shrink Tube

1/4" (6mm) • 3/8" (9mm) • 1/2" (12mm) • 3/4" (19mm)

Part #	Description	Length
18051	White Heat Shrink Tube 1/4" (6mm)	5'
18053	White Heat Shrink Tube 3/8" (9mm)	5'
18055	White Heat Shrink Tube 1/2" (12mm)	5'
18057	White Heat Shrink Tube 3/4" (19mm)	5'
18052	Yellow Heat Shrink Tube 1/4" (6mm)	5'
18054	Yellow Heat Shrink Tube 3/8" (9mm)	5'
18056	Yellow Heat Shrink Tube 1/2" (12mm)	5'
18058	Yellow Heat Shrink Tube 3/4" (19mm)	5'

### Non-Adhesive

1/4" (6mm) • 3/8" (9mm) • 1/2" (12mm) • 3/4" (19mm)

Part #	Description	Length
18111	White Non-Adhesive Tag 1/4" (6mm)	5'
18112	White Non-Adhesive Tag 3/8" (9mm)	5'
18113	White Non-Adhesive Tag 1/2" (12mm)	5'
18114	White Non-Adhesive Tag 3/4" (19mm)	5'
18115	Yellow Non-Adhesive Tag 1/4" (6mm)	5'
18116	Yellow Non-Adhesive Tag 3/8" (9mm)	5'
18117	Yellow Non-Adhesive Tag 1/2" (12mm)	5'
18118	Yellow Non-Adhesive Tag 3/4" (19mm)	5'

### Label Colors



## Labels that stick and stay stuck.

RHINO labels are easy to use and super-strong. Thanks to industrial-strength adhesives, they deliver the lasting durability and legibility you demand – for a multitude of applications. To meet your high standards, RHINO labels are designed to work exclusively with RHINO printers and perform on a variety of surfaces (smooth, curved, textured and highly textured).

- Industrial-strength adhesives help these labels stick and stay stuck – in harsh worksite conditions.
- Thermal transfer print technology produces labels that are durable, smear-proof and resistant to chemicals, solvents, heat, UV and more.

### Ideal Label Applications

#### Flexible Nylon

Wire, cable, curved & highly textured surfaces

#### Permanent Polyester

Flat surfaces such as panels; textured and rough surfaces; can be used outdoors

#### Vinyl

Flat or curved surfaces; can be used outdoors

#### Heat Shrink Tubes

Wires & cables; slides on and won't fall off

#### Non-adhesive Tags

Inserts or other applications where adhesive is not required



Easy-to-peel split backing

RHINO6000 SINGLE UNIT (BOXED)	RHINO6000 HARD CASE KIT
Part No. 1734519	Part No. 1734520
UPC: 0 71701 12173	UPC: 0 71701 12174
Box includes:	Hard case kit includes:
Rhino6000 printer	Rhino6000 printer
1" black on white flexible nylon tape	Rhino connect software
Rechargeable lithium-ion battery pack	Durable hard carry case
AC adaptor	1" black on white flexible nylon label
Quick reference guide	3/8" black on white vinyl label cartridge
Registration card	Rechargeable lithium-ion battery pack
	AC adaptor and USB cable
PRODUCT SPECIFICATIONS:	PRODUCT SPECIFICATIONS:
Quick-charge lithium-ion rechargeable battery and on-screen battery life indicator	Quick-charge lithium-ion rechargeable battery and on-screen battery life indicator
1 year limited warranty	1 year limited warranty
Unit weight: 1.98 lbs	Unit weight: 5.4 lbs
Units per master carton:	Units per master carton:
Master carton dimensions (LxWxH): 9.7" x 4.9" x 2.6"	Master carton dimensions (LxWxH): 14" x 18" x 4"
Master carton weight:	Master carton weight:

For more information visit: [www.dymo.com](http://www.dymo.com) or call 1 (800) 426-7827. Images and specifications subject to change without notice.

DYMO and the DYMO logo are trademarks or registered trademarks of Sanford, L.P. or its affiliates. All other trademarks are the property of their respective owners. All individual and company names used on sample labels are fictitious.

#### Produced by:

DYMO, Atlanta, GA 30328  
800-426-7827: [www.dymo.com](http://www.dymo.com)  
©2010 Sanford, L.P.  
A Newell Rubbermaid Company

S4157  
09-0794



**NewellRubbermaid**  
Brands That Matter