

Part Number	G2162 -- EGVHVA102-102UKLPS6-IP44 Basic, Non-Surge
Power Configuration	16A, 230V, 3.6kW
Physical Configuration	39 in / 978 mm Vertical



Description	The G2162 -- EGVHVA102-102UKLPS6-IP44 non-surge unit is ideal for facilities already equipped with surge protection.
Product Summary	G2162 -- EGVHVA102-102UKLPS6-IP44 - Non-Surge, 16A, 230V, Vertical, (10) BS1363, power switch, 3 m power cord with 2P+E
Monitoring	None
Plug Form	 2P+E
Receptacle	 BS1363 (Quantity: 10)



G2162 -- EGVHVA102-102UKLPS6-IP44 - Product Specification and Options

Quantity Of Inputs	1
Voltage	230V
Current	16A
VA per Input (Load Capacity)	3.6kW
Frequency	50/60 Hz
Over Current Protection	None
Switch	Green neon with protective cover
Power Cable Wire Gauge	2.5mm ² H07RN-F
Power Cable Length	3m
Plug Type	IEC60309 2P + E, 16A, 250V, Splashproof IP44
Receptacle/Socket Type #1	BS1363
Quantity on Face #1	10
Style #1	Individual - Left Hand Angled
Maximum Output per Receptacle/Socket #1	13A
Voltage per Receptacle/Socket #1	230V
Heavy Steel -Black Powder Coat	Yes
Configuration	39in / 978mm Vertical Rackmount
GE Vertical Mounting Bracket	Yes
Toolless Mounting Hardware - Center to Center Spacing	933.45 mm
Product Warranty	Lifetime
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55022 and EN 55024
Certification/Agency Approvals	RoHS Compliant
Chassis Dimensions (LxWxD)	978mm x 54mm x 50mm
Shipped Weight	9lbs (4.08kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Geist Asia

Hong Kong
Tel: +852 90361927
Email: salesasia@geistglobal.com