


A.  
System  
Overview

## 4-Way Adhesive Backed Cable Tie Mounts

B1.  
Cable Ties

- Allow cable tie entry from all four sides
- Available in multiple sizes to match application load requirements
- Produced 2-up or 4-up for fast and easy liner removal to speed installation

B2.  
Cable  
Accessories



C1.  
Wiring  
Duct

| Part Number | Used with<br>Cable Ties‡ | Material | Color | Environment | Mounting<br>Method* | Std.<br>Pkg.<br>Qty. | Std.<br>Ctn.<br>Qty. |
|-------------|--------------------------|----------|-------|-------------|---------------------|----------------------|----------------------|
|-------------|--------------------------|----------|-------|-------------|---------------------|----------------------|----------------------|

### 4-Way Mounts with Pre-Installed Adhesive

|              |                            |                                |       |                        |         |     |      |
|--------------|----------------------------|--------------------------------|-------|------------------------|---------|-----|------|
| ABM1M-A-C    | M                          | Nylon 6.6                      | White | Indoors                | Rubber  | 100 | 500  |
| ABM1M-AT-C   |                            | Nylon 6.6                      | White | Indoors/High Temp      | Acrylic | 100 | 500  |
| ABMM-A-C     | M, I                       | ABS                            | White | Indoors                | Rubber  | 100 | 500  |
| ABMM-AT-C    |                            | ABS                            | White | Indoors/High Temp      | Acrylic | 100 | 500  |
| ABMM-AT-C0   |                            | Weather Resistant<br>ABS       | Black | Outdoors/<br>High Temp | Acrylic | 100 | 500  |
| ABM2S-A-C    | M, I, S                    | ABS                            | White | Indoors                | Rubber  | 100 | 500  |
| ABM2S-A-C14  |                            | ABS                            | Gray  | Indoors                | Rubber  | 100 | 500  |
| ABM2S-A-C15  |                            | ABS                            | Ivory | Indoors                | Rubber  | 100 | 500  |
| ABM2S-AT-C   |                            | ABS                            | White | Indoors/High Temp      | Acrylic | 100 | 500  |
| ABM2S-AT-C0  |                            | Weather Resistant<br>ABS       | Black | Outdoors/<br>High Temp | Acrylic | 100 | 500  |
| ABM100-A-C   |                            | Nylon 6.6                      | White | Indoors                | Rubber  | 100 | 1000 |
| ABM100-A-C15 |                            | Nylon 6.6                      | Ivory | Indoors                | Rubber  | 100 | 1000 |
| ABM100-AT-C  |                            | Nylon 6.6                      | White | Indoors/High Temp      | Acrylic | 100 | 1000 |
| ABM100-AT-C0 |                            | Weather Resistant<br>Nylon 6.6 | Black | Outdoors/<br>High Temp | Acrylic | 100 | 1000 |
| ABM112-A-C   |                            | Nylon 6.6                      | White | Indoors                | Rubber  | 100 | 500  |
| ABM112-AT-C  |                            | Nylon 6.6                      | White | Indoors/High Temp      | Acrylic | 100 | 1000 |
| ABM112-AT-C0 |                            | Weather Resistant<br>Nylon 6.6 | Black | Outdoors/<br>High Temp | Acrylic | 100 | 1000 |
| ABM3H-A-L    | M, I, S, HS,<br>LH, H, HLM | Nylon 6.6                      | White | Indoors                | Rubber  | 50  | 500  |
| ABM3H-AT-L   |                            | Nylon 6.6                      | White | Indoors/High Temp      | Acrylic | 50  | 500  |
| ABM4H-A-L    |                            | Nylon 6.6                      | White | Indoors                | Rubber  | 50  | 500  |
| ABM4H-AT-L   |                            | Nylon 6.6                      | White | Indoors/High Temp      | Acrylic | 50  | 500  |

‡Cable tie cross section sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, and H = Heavy, HLM = Miniature Tak-Ty® Hook & Loop Ties.

\*For proper selection of adhesives see page B2.54.

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index

## 4-Way Adhesive Backed Cable Tie Mounts (continued)

| Part Number                                                                | Used with Cable Ties‡   | Material                  | Color   | Environment | Mounting Method*                                 | Std. Pkg. Qty. | Std. Ctn. Qty. |
|----------------------------------------------------------------------------|-------------------------|---------------------------|---------|-------------|--------------------------------------------------|----------------|----------------|
| <b>4-Way Mounts for Installation with Screws or User-Supplied Adhesive</b> |                         |                           |         |             |                                                  |                |                |
| ABMM-D                                                                     | M, I                    | ABS                       | White   | Indoors     | User Supplied Adhesive                           | 500            | 5000           |
| ABM2S-S6-D                                                                 | M, I, S                 | ABS                       | White   | Indoors     | User Supplied Adhesive and/or two #6 (M3) Screws | 500            | 5000           |
| ABM100-S6-C                                                                |                         | Nylon 6.6                 | White   | Indoors     |                                                  | 100            | 1000           |
| ABM100-S6-C69                                                              |                         | Flame Retardant Nylon 6.6 | Natural | Indoors     | User Supplied Adhesive and/or #6 (M3) Screw      | 100            | 1000           |
| ABM112-S6-C                                                                |                         | Nylon 6.6                 | White   | Indoors     | User Supplied Adhesive and/or Two #6 (M3) Screws | 100            | 1000           |
| ABM112-S6-C69                                                              |                         | Flame Retardant Nylon 6.6 | Natural | Indoors     |                                                  | 100            | 500            |
| ABM3H-S6-T                                                                 | M, I, S, HS, LH, H, HLM | Nylon 6.6                 | White   | Indoors     |                                                  | 200            | 2000           |
| ABM4H-S6-T                                                                 |                         | Nylon 6.6                 | White   | Indoors     |                                                  | 200            | 1000           |

‡Cable tie cross section sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, and H = Heavy, HLM = Miniature Tak-Ty® Hook & Loop Ties.

\*For proper selection of adhesives see page B2.54.

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index