

### PatchRunner™ Vertical Cable Management System

- High density minimizes area required for network layout, freeing up valuable floor space
- Curved cable management fingers support cables as they transition to the vertical pathway eliminating the need for horizontal managers
- Individual fingers can be removed without the use of a tool for routing of large cable bundles
- Fingers align with rack spaces simplifying cable routing
- Slack management spools organize and manage patch cord slack allowing standardization of patch cords
- Optional hinged doors provide easy access to vertical pathway; purchased separately from manager
- Available in 7 foot and 8 foot versions



PRV8

PRVF8



PRD

Part Number	Part Description	No. of Rack Spaces <sup>^</sup>	Std. Pkg. Qty.	Std. Ctn. Qty.
<b>Vertical Manager – Manage Cable on Front and Rear of Rack*</b>				
<b>PRV6*</b>	Vertical cable manager, spools are not included. Dimensions: 84"H x 6"W x 16.4"D (2133.6mm x 152.4mm x 416.6mm)	45	1	—
<b>PRV8*</b>	Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 8.0"W x 16.4"D (2131mm x 203mm x 417mm)	45	1	—
<b>PRV10*</b>	Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 10.0"W x 16.4"D (2131mm x 254mm x 417mm)	45	1	—
<b>PRV12*</b>	Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 12.0"W x 16.4"D (2131mm x 305mm x 417mm)	45	1	—
<b>PRV15*</b>	Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 15.0"W x 16.4"D (2131mm x 381mm x 417mm)	45	1	—

#### Vertical Manager – Manage Cable on Front of Rack Only\*

<b>PRVF6*</b>	Vertical cable manager, spools are not included. Dimensions: 83.9"H x 6.0"W x 9.7"D (2131mm x 152mm x 246mm)	45	1	—
<b>PRVF8*</b>	Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 8.0"W x 9.7"D (2131mm x 203mm x 246mm)	45	1	—
<b>PRVF10*</b>	Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 10.0"W x 9.7"D (2131mm x 254mm x 246mm)	45	1	—
<b>PRVF12*</b>	Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 12.0"W x 9.7"D (2131mm x 305mm x 246mm)	45	1	—
<b>PRVF15*</b>	Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 15.0"W x 9.7"D (2131mm x 381mm x 246mm)	45	1	—

#### PatchRunner™ Doors

<b>PRD6*</b>	Dual hinged metal door. Dimensions: 82.8"H x 6.1"W x 1.6"D (2104mm x 206mm x 40mm)	45	1	—
<b>PRD8*</b>	Dual hinged metal door. Dimensions: 82.8"H x 8.1"W x 1.6"D (2104mm x 206mm x 40mm)	45	1	—
<b>PRD10*</b>	Dual hinged metal door. Dimensions: 82.8"H x 10.1"W x 1.6"D (2104mm x 257mm x 40mm)	45	1	—
<b>PRD12*</b>	Dual hinged metal door. Dimensions: 82.8"H x 12.1"W x 1.6"D (2104mm x 308mm x 40mm)	45	1	—

<sup>^</sup>One rack space = 1.75" (44.45mm).

All product color is black.

\*For part numbers that fit 8' rack, add "96" to end of part number. Overall height for managers is 95.5" (2426mm). Overall door height is 94.4" (2399mm).

### PatchRunner™ Vertical Cable Management System (continued)



PRSHD8



PED



PREP



PEDK



PRSP7



CRTW

Part Number	Part Description	No. of Rack Spaces^	Std. Pkg. Qty.	Std. Ctn. Qty.
PRD15*	Dual hinged metal door. Dimensions: 82.8"H x 15.1"W x 1.6"D (2104mm x 384mm x 40mm)	45	1	—
PRSHD6	Single hinged metal door. Dimensions: 80.7"H x 6.0"W x .8"D (2049mm x 152mm x 20mm)	45	1	—
PRSHD8	Single hinged metal door. Dimensions: 80.7"H x 8.0"W x .8"D (2049mm x 203mm x 20mm)	45	1	—
PRSHD12	Single hinged metal door. Dimensions: 80.7"H x 12.0"W x .8"D (2049mm x 305mm x 20mm)	45	1	—

#### PatchRunner™ High Capacity Dual Hinged Doors

PED6	Dual hinged metal door. Dimensions: 82.8"H x 6.1"W x 1.7"D (2103mm x 155mm x 43mm) Requires the use of PEDK6 door bracket.	45	1	—
PED8	Dual hinged metal door. Dimensions: 82.8"H x 8.1"W x 1.7"D (2103mm x 206mm x 43mm) Requires the use of PEDK8 door bracket.	45	1	—
PED10	Dual hinged metal door. Dimensions: 82.8"H x 10.1"W x 1.7"D (2103mm x 256mm x 43mm) Requires the use of PEDK10 door bracket.	45	1	—
PED12	Dual hinged metal door. Dimensions: 82.8"H x 12.1"W x 1.7"D (2103mm x 307mm x 43mm) Requires the use of PEDK12 door bracket.	45	1	—

#### PED Door Brackets

PEDK6	Bracket kit for 6" wide PatchRunner™ Dual Hinged Door PED6.	—	1	10
PEDK8	Bracket kit for 8" wide PatchRunner™ Dual Hinged Door PED8.	—	1	10
PEDK10	Bracket kit for 10" wide PatchRunner™ Dual Hinged Door PED10.	—	1	10
PEDK12	Bracket kit for 12" wide PatchRunner™ Dual Hinged Door PED12.	—	1	10

#### Accessories

PRSP7	Molded plastic slack spool, front only. Dimensions: 7.0"D x 1.3" dia. (178mm x 32mm)	—	1	10
PRSP5	Molded plastic slack spool, front or rear. Dimensions: 5.25"D x 1.3" dia. (133mm x 32mm)	—	1	10
PREP	End panel Dimensions: 82.5"H x 14.5"W x .7"D (2095mm x 367mm x 18mm)	—	1	—
PREP96	End panel 8' Dimensions: 94.1"H x 14.5"W x .7"D (2390mm x 367mm x 18mm)	—	1	—
CRTW	Rack top trough with waterfall creates pathway above rack, for use with R2P, PRV6, PRV8, PRV10, PRV12, and PRV15. Dimensions: 3.3"H x 23.4"W x 14.0"D (84mm x 594mm x 356mm)	—	1	—
WR5E-X	Snap-on finger cable retainers.	—	10	100

^One rack space = 1.75" (44.45mm).

All product color is black.

\*For part numbers that fit 8' rack, add "96" to end of part number. Overall height for managers is 95.5" (2426mm). Overall door height is 94.4" (2399mm).