

2 Post Cable Management Rack System and Accessories

- Rack space identification allows quick and easy location of rack mount items
- 3" Rack is UL listed for 1,000 lbs. load rating
- 6" Rack is UL listed for 1,500 lbs. load rating
- Double-sided #12-24 EIA universal mounting hole spacing
- 24 #12-24 mounting screws included
- Can be used with all Panduit cable management and patch panel products in addition to any industry standard 19" components
- Paint piercing washers included to electrically bond rack for simplified grounding; for the complete grounding solution, see the StructuredGround™ Kits for Racks
- 6" rack, R2P6S is compatible with Patchrunner™ and High Capacity PatchRunner™ products only



R2P6S



R2P



R2PAE1



RFAKIT



RWMPV45E



RWMPVHC45E



RNRV6



RNRV10



RWMPVF45E



RWMPVHCF45E

Part Number	Part Description	No. of Rack Spaces [^]	Std. Pkg. Qty.	Std. Ctn. Qty.
6" Channel Rack – Numbered Up				
R2P6S	19" EIA rack, 6" channel, steel. Dimensions: 84.0"H x 20.3"W x 6"D (2134mm x 514mm x 152mm). Note: This rack is compatible with Patchrunner and High Capacity Patchrunners only.	45	1	—
3" Channel Racks – Numbered Up				
R2P96	19" EIA rack, aluminum. Dimensions: 96.0"H x 20.3"W x 3.0"D (2134mm x 514mm x 76mm).	52	1	—
R2P	19" EIA rack, aluminum. Dimensions: 84.0"H x 20.3"W x 3.0"D (2134mm x 514mm x 76mm).	45	1	—
R2P48	19" EIA rack, aluminum. Dimensions: 48.0"H x 20.3"W x 3.0"D (1219mm x 514mm x 76mm).	24	1	—
R2PW	23" EIA rack, aluminum. Dimensions: 84.0"H x 24.3"W x 3.0"D (2134mm x 616mm x 76mm).	45	1	—
2 Post Rack Accessories				
R2PAE1	2 post rack thermal duct for use with Cisco* 6509 and 6509E Catalyst switches.	—	1	—
RFAKIT	Rack anchor kit for concrete floor (set of four).	—	1	10
S1224-C	#12-24 x .5" mounting screws.	—	100	1000
2 Post 3" Channel Racks Numbered Up with Dual-Sided Vertical Cable Managers				
RWMPV45E	#12-24 threaded equipment mounting rails with front and rear manager. Dimensions: 84.0"H x 25.5"W x 15"D (2134mm x 648mm x 381mm)	45	1	—
RWMPVHC45E	#12-24 threaded equipment mounting rails with front and rear manager. Dimensions: 84.0"H x 27.4"W x 15"D (2134mm x 695mm x 381mm)	45	1	—
RNRV6	#12-24 threaded equipment mounting rails with front and rear manager. Dimensions: 84.0"H x 27.1"W x 15"D (2134mm x 689mm x 381mm)	45	1	—
RNRV10	#12-24 threaded equipment mounting rails with front and rear manager. Dimensions: 84.0"H x 30.4"W x 15"D (2134mm x 773mm x 381mm)	45	1	—
2 Post 3" Channel Racks Numbered Up with Single Sided Vertical Cable Managers				
RWMPVF45E	#12-24 threaded equipment mounting rails with a front only manager. Dimensions: 84.0"H x 25.5"W x 15"D (2134mm x 648mm x 381mm)	45	1	—
RWMPVHCF45E	#12-24 threaded equipment mounting rails with a front only manager. Dimensions: 84.0"H x 27.4"W x 15"D (2134mm x 695mm x 381mm)	45	1	—

[^]One rack space = 1.75" (44.45mm).

All product color is black.

*Cisco is a registered trademark of Cisco Technology, Inc.