


3

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA13-A THRU PCA13-Z	'A' THRU 'Z'	30	300	1	10	.130" - .150"
PCA13-A-J	'A' - 'J' [3 EA.]	30	300	1	10	.130" - .150"
PCA13-K-T	'K' - 'T' [3 EA.]	30	300	1	10	.130" - .150"
PCA13-U-Z	'U' - 'Z' [3 EA.]	30	300	1	10	.130" - .150"
PCA13-0 THRU PCA13-9	'0' THRU '9'	30	300	1	10	.130" - .150"
PCA13-0-9	'0' - '9' [3 EA.]	30	300	1	10	.130" - .150"
PCA13-MIN	' - '	30	300	1	10	.130" - .150"
PCA13-PLS	' + '	30	300	1	10	.130" - .150"



3

- NOTES:
 1. COLOR: WHITE WITH BLACK LEGENDS.
 2. MILLIMETERS ARE IN [].

										CAD FILENAME/LAYERS		100281DF-DC-C10346/03C				
										PANDUIT CORP. TINLEY PARK, ILLINOIS						
										CUSTOMER DRAWING PCA13-* CLIP-ON WIRE MARKER						
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .062 (.XXX) ± .015 (.XX) ± .031 ANGLES ±			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
2	8/11/10	RVU		UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.		6079	R									
1	7-15-07	RVU		ADDED TOLERANCE AND REVISED TABLE.		4881	R				DRAWN BY RVU	MAT'L:		SCALE		
0	10-5-06	RVU		DRAWING RELEASE		4715	R				DATE 9-5-04	WHITE MARKER -ACETAL		DRAWING NO. C10346		DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP	CHK'D					