



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

BELOW VIEWS SHOWN
WITHOUT DUSTCAPS



NOTES:

1. SEE CURRENT CATALOG:
A. FOR TECHNICAL AND OPERATING SPECIFICATIONS.
B. FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. MATERIALS:
A. ENCLOSURE: COMPOSITE PLASTIC WITH METAL FASTENERS.
B. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
3. DIMENSIONS IN BRACKETS ARE METRIC [mm].
4. PART INCLUDES:
1- BASE ASSEMBLY
1- FACEPLATE
1- FIBER COVER
1- PG21 CORD GRIP
4- ULTIMATE ID LABELS AND COVERS
4- 6-32 X 3/8" PHILLIPS DRIVE SCREWS



ISOMETRIC VIEW
SHOWN WITH DUSTCAPS

PANDUIT P/N	WEIGHT
FDME8RG	0.72 LB/PCS [325 g/PCS]

										8-PORT INDUSTRIALNET™ DIN RAIL MOUNT FIBER ENCLOSURE CUSTOMER DRAWING					
										PANDUIT® TINLEY PARK, IL 60487		T.I. NUMBER			
										THIRD ANGLE PROJECTION		PRODUCT SPEC/ PKG SPEC			
												DRAWING FILENAME 11F151AE_DC/OOB			
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°		SCALE NONE			
												PART NO. FDME8RG			
1	03-29-12	JGD	JAWI	RELEASE TO PRODUCTION	11F151AE-DC	JGD	RWB			DATE 01-17-12	REVIEW DRAWING NUMBERS		DRAWING NO. 11F151AE-DC		SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D JGD					