


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
CFPF12**-2G	.10 LB/1 PCS (45 g/1 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THESE PARTS.
3. THIS PART INCLUDES SIX (6) CHF2M**, X 1.0 ONE (1) CB**-2G, AND FOUR (4) #6-32 SCREWS (00058-03**).



P/N: CB**-2G
REFERENCE CUSTOMER DRAWING
00058-02 FOR DIMENSIONS



P/N: CHF2M**
REFERENCE CUSTOMER DRAWING
35544-27 FOR DIMENSIONS

# 35544-27 FOR DIMENSIONS										CAD FILENAME/LAYERS										MO0142BD_DC_00B.PRT									
																				PANDUIT CORP. TINLEY PARK, ILLINOIS  CLASSIC SERIES DOUBLE GANG (CFPF12**-2G) CUSTOMER DRAWING									
																				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±									
																				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.									
																				SCALE NONE									
																				DRAWING NO.									
																				A									
																				00142-03									
																				SIZE									