



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
NKPPA24FMY	8.05 LB/10 PCS (3653.6 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
- THE FLUSH MOUNT PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTENTS:
 - (1) - 24 PORT ANGLED STAMPING
 - (6) - 4 POSITION FACEPLATE (ASSEMBLED TO PANEL)
 - (1) - SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - (1) - SCREW KIT (INCLUDES FOUR M6 SCREWS)
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.



MODEL FILENAME	NC1667AD_LAKTIPAZ24FMY_ASMBLL0.PRT	SIZE
DRAWING FILENAME	MD2479DC_LDCSS_L00A.PRT	A

NETWORK SYSTEMS

MAY 25 2006

ENGINEERING DEPT

NETKEY ANGLED 24 PORT FLUSH MOUNT
MODULAR PATCH PANEL CUSTOMER DRAWING

 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: .XXX1 ± .0001 .XXX1 ± .0001 .XXX1 ± .0001 ANGLES ± .0001	U.S. NUMBER	N/A
	THIRD ANGLE PROJECTION	PRODUCT SPEC	N/A
		WORK INSTRUCTION	N/A
		SCALE	NONE
DRAWN BY JSP	DATED BY	PART NO.	NKPPA24FMY
DATE 4-18-06	PANEL: 20 GAGE C.R.S. FACEPLATE: ABS	DRAWING NO.	02479-095

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	QTH
R	4-18-06	JSP		RELEASED TO PRODUCTION	02479-095				