




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANOUT CORP.

PANOUT P/N	WEIGHT
NKPPA48HDY	4.25 LB/10 PCS (1935.9 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
- THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTENTS:
 - 48 PORT ANGLED STAMPING
 - 8 POSITION FACEPLATE (ASSEMBLED TO PANEL)
 - SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - SCREW KIT (INCLUDES FOUR M6 SCREWS)
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



NETWORK SYSTEMS

MAY 25 2006

ENGINEERING DEPT

MODEL FILENAME: M01668AA NKPPA48-HD-CLASSM1.DWG.PRT SIZE: A

DRAWING FILENAME: M02479D010097100A.PRT

NETKEY 48 PORT ANGLED HIGH DENSITY MODULAR PATCH PANEL CUSTOMER DRAWING

PANOUT™
TINLEY PARK, ILL 60477

ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
0.001 ± 0.0001 (0.0025 ± 0.0001) ANGLES ± 0.001

DRAWN BY: JSP

DATE: 5-11-06

CHK'D: JSP

INTERNAL

STAMPING:
20 GAGE C.R.S.
FACEPLATE: ABS

FILE NUMBER: N/A

PRODUCT SPEC: N/A

REF. INSTRUCTION: N/A

SCALE: NONE

PART NO.: NKPPA48HDY

DRAWING NO.: 02479-097

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	3-11-06	JSP		RELEASED TO PRODUCTION	02479-097				