





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	DESCRIPTION	WEIGHT
NKRPMR**	MODULE WITH RED INSERT	6.51g/PC
NKRPMY**	MODULE WITH YELLOW INSERT	
NKRPMW**	MODULE WITH WHITE INSERT	

- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 3. DIMENSIONS IN PARENTHESSES ARE IN METRIC.



MODEL FILENAME MO2403AH_NK_110_RCA_ASSY_00.PRT		DRAWING FILENAME MO2403BC_DC09_00A.PRT		SIZE A					
TITLE NETKEY™ RCA PUNCHDOWN MODULE CUSTOMER DRAWING									
 PANDUIT CORP. TINLEY PARK, IL 60477		I.I. NUMBER PRODUCT SPEC WORK INSTRUCTION SCALE FULL		PART NO. NKRPM**					
ALL DIMENSIONS ARE GIVEN IN INCHES. DIMENSIONAL TOLERANCES ARE: (.X) : (.XX) : (.XXX) : ANGLES :		REVIEW DRAWING NUMBERS DRAWN BY MDJr DATE 4-18-06 CHK'D MDJr		MATERIAL ABS					
REV	DATE	BY	CHK	DESCRIPTION	ECON	R	CUST	SUP	OTH
R	4-18-06	MDJr		RELEASED TO PRODUCTION	02403-09				