


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


| PANDUIT PART# | DESCRIPTION | WEIGHT |
|---------------|---|-----------------------------------|
| NK6TM** | 8 POSITION, 8 WIRE UNIVERSAL MODULE. TERMINATION CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES. | 1.43 LB/100 PCS (649g/100 PCS) |



NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND PACKAGE QUANTITY.
- MATERIAL:
MODULE HOUSING- ABS
NOMINAL WALL THICKNESS .078(2.0).
PRESERVATION CAP-PC
- ALL NETKEY CAT6, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION PAIR MODULAR PLUGS WITHOUT DAMAGE.
- THIS PART IS DESIGNED FOR USE WITH STANDARD KEYSTONE OPENINGS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.

PANEL OPENING REQUIREMENTS
 PANEL THICKNESS: .048" - .058"
 (1.22mm - 1.47mm)



| | | |
|--|------------------------|-------------------------|
| MODEL FILENAME M01336A1_TX6P_KSTN_ASSBY_00.PRT | | SIZE A |
| DRAWING FILENAME M01336EJ_DC41_00A.PRT | | |
| TITLE NETKEY CATEGORY 6 JACK MODULE CUSTOMER DRAWING | | |
| <p>PANDUIT™ CORP. TINLEY PARK, ILL 60477</p> | I.I. NUMBER | |
| | PRODUCT SPEC | |
| <p>THIRD ANGLE PROJECTION</p> | WORK INSTRUCTION | |
| | SCALE | NONE |
| DRAWN BY MDJr | REVIEW DRAWING NUMBERS | PART NO. NK6TM** |
| DATE 5-6-03 | | DRAWING NO. 01336-41 |
| CHK'D | | |

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP | OTH |
|-----|---------|------|-----|------------------------|----------|---|------|-----|-----|
| R | 5-12-03 | MDJr | | RELEASED TO PRODUCTION | 01336-41 | | | | |