





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
HB1A1M2BN12E1	8 lb (3.6 kg)

- NOTES:
- IDENTIFICATION: 1RU HORIZONTAL, (12) 5-20R METERED 120V / 30A / SINGLE-PHASE POU
 - ACCESSORY COMPONENTS:
(4) 10-32 x 1/2" MOUNTING SCREWS
(4) 12-24 x 1/2" MOUNTING SCREWS
(2) MOUNTING BRACKETS
 - DIMENSIONS IN PARENTHESES ARE METRIC (mm).
 - POWER METER - RED, 4-DIGIT LED CONTINUOUSLY SCROLLS THROUGH POWER FACTOR, AMPS, VOLTS (RMS), AND REAL POWER IN WATTS (RMS).
 - UL® & c-UL® LISTED 60950 AND NOM COMPLIANT.
 - RoHS COMPLIANT.
 - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
 - MAXIMUM AVAILABLE INPUT POWER = 2.9 KW
 - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



REV	DATE	BY	CHK	DESCRIPTION	ECN	RI	CUST	SUP	OTH
01A	9-19-12	PIP	MRWA	B. ADDED NOTE #9. C. UPDATED NOTE #2 & 5. D. UPDATED RECEPTACLE COUNT.	09V098DC				
00B	12-20-11	MRWA	KRKE	A. UPDATED NOTE 8	09V098DC				
00A	2-24-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098DC				

MODEL FILENAME:		09V098DC/01.PRT	
CAD FILENAME/LAYERS		09V098DC_DC/01A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
1RU HORIZONTAL, (12) 5-20R METERED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES		[METRIC - MILLIMETER]	
X.X +/- 0.03		X +/- 0.8	
X.XX +/- 0.015		X.X +/- 0.4	
X.XXX +/- 0.005		X.XX +/- 0.13	
		ANGLE	
		+/- 1°	
		INCHES, THIRD ANGLE PROJECTION	
DRAWN BY		SCALE	
MAV		NONE	
DATE		DRAWING NO.	
2-24-11		09V098DC	
CHK'D		DWG	
KRKE		B	
		SIZE	