




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



Part Number	Type	Dim "A"	Dim "B"	LABELS PER PKG.	PKG. TYPE
PPS0404WSL1-TER	Pre-Printed Non-Reflective Polyester (GMY4-HT+GMOM50)	4.00 [101.6]	4.00 [101.6]	50	CARDS
PPS0204WSL1-TER		4.00 [101.6]	2.00 [50.8]		
PPS0204WSL1-DCC		4.00 [101.6]	2.00 [50.8]		
PPS0103WSL1-ADI		3.00 [76.2]	1.50 [38.1]		
PPS0103WSL1-SLC		3.00 [76.2]	1.50 [38.1]		
PPS0206WSR1-PS	Pre-Printed Reflective Vinyl (GMRS+GMY4-C)	6.00 [152.4]	1.75 [44.45]		
PPS0206BSR1-MD		6.00 [152.4]	1.75 [44.45]		
PPS0206BSR1-SD		6.00 [152.4]	1.75 [44.45]		
C600X175SP1-AD	Customer Printable Non-Reflective Polyester (GMY4-HT+GMY4-C)	6.00 [152.4]	1.75 [44.45]		ROLLS
C600X175SP1-DD		6.00 [152.4]	1.75 [44.45]		
C400X400SP1-DD		4.00 [101.6]	4.00 [101.6]		
C400X200SP1-AD		4.00 [101.6]	2.00 [50.8]		
C400X400SP1-PS		4.00 [101.6]	4.00 [101.6]		
C400X400SP1-DSM		4.00 [101.6]	4.00 [101.6]		
C400X400SP1-ASM		4.00 [101.6]	4.00 [101.6]		
C400X400SL1-OL		4.00 [101.6]	4.00 [101.6]		
C400X200SL1-OL	Clear Overlamine Component Label (GMY4-C)	4.00 [101.6]	2.00 [50.8]	250	
C600X175SL1-OL		6.00 [152.4]	1.75 [44.45]		
C300X150SL1-OL		3.00 [76.2]	1.50 [38.1]		

Notes:

1. [] INDICATE MILLIMETERS
2. VISIT WWW.PANDUIT.COM FOR LABEL LEGEND
3. OVERLAMINATE AND CUSTOMER PRINTABLE ON ROLLS. ALL PRE-PRINTED LABELS WILL BE ON INDIVIDUAL CARDS.

							TITLE Solar Labels CUSTOMER DRAWING ITEM REVISION NAME 12I119BE/00 DATASET FILE NAME 12I119BE_DC-C11042/00A UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 [2.54] .XXX ± .031 [.97] .XX ± .064 [1.63] ANGLES ± 5 °  THIRD ANGLE PROJECTION MATERIAL : SEE TABLE DRAWING NUMBER : C11042 DRAWN BY JHAC DATE 2/20/13 CHK MSAD SCALE NTS SHT 1 OF 1 SIZE A				
01	4/15/13	JHAC	MJPF	MSAD	ADDED NEW PARTS TO TABLE	GAECN00775					
00	2/20/13	JHAC	MJPF	MSAD	DRAWING RELEASE	GAECN00611					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN					