


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE SHEETS 2, 3 & 4 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITIES.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.




DUPLEXED LC CONNECTORS  
(PRINTED CABLE SIDE B)

DUPLEXED LC CONNECTORS  
(PRINTED CABLE SIDE A)

FIBER OPTIC PATCH CORD  
DUPLEX LC TO LC CONFIGURATION  
CUSTOMER DRAWING



**PANDUIT**™  
CORP.  
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES  
UNLESS OTHERWISE SPECIFIED.  
DIMENSIONAL TOLERANCES ARE:  
(.X) ±.010 (0.3)  
(.XX) ±.03 (0.8) ANGLES

DRAWING FILENAME  
M02779BC\_DC/01A

SCALE  
NONE

DRAWN BY  
MC

REVIEW DRAWING NUMBERS

PART NO.  
SEE SHEETS 2, 3 & 4

DATE  
04-27-07

DRAWING NO.  
02779-11  
SHEET 1 OF 4  
SIZE  
A



CHK'D  
RAF

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-11				

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX LC TO LC FIBER OPTIC PATCH CORD							
PANDUIT PART NO.	CABLE				LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5E10-10M*Y	RISER (OFNR)	50/125um	DUPLEX 1.6mm ZIPCORD	ORANGE	0.25dB	20dB	BLACK
F6E10-10M*Y		62.5/125um					ELECTRIC IVORY
FXE10-10M*Y		10GbE OM3		AQUA	0.25dB	26dB	AQUA
FXOE10-10M*		OPTIMIZED 10GbE OM3			0.15dB	26dB	
FZE10-10M*		10GbE OM4		AQUA	0.25dB	26dB	AQUA
FZOE10-10M*		OPTIMIZED 10GbE OM4			0.15dB	26dB	
F9E10-10M*Y		9/125um OS1		YELLOW	0.35dB	55dB	BLUE


\* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC PATCH CORD DUPLEX LC TO LC CONFIGURATION CUSTOMER DRAWING					
										 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477					
										 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03   (.XXX) ±.010   (0.3) ±.01 ANGLES		DRAWING FILENAME M02779BC_DC/01A SCALE NONE	
										DRAWN BY MC		REVIEW DRAWING NUMBERS		PART NO. SEE SHEETS 2, 3 & 4	
										DATE 04-27-07		DRAWING NO. 02779-11		SIZE A	
01	09-09-09	EFK	RELEASED TO PRODUCTION			02779-11					CHK'D	RAF	SHEET 2 OF 4		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH						


DUPLEX LC TO LC FIBER OPTIC PATCH CORD							
PANDUIT PART NO.	CABLE				LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5PE10-10M*	PLENUM (OFNP)	50/125um OM2	DUPLEX 1.6mm ZIPCORD	ORANGE	0.25dB	20dB	BLACK
F6PE10-10M*		62.5/125um OM1					ELECTRIC IVORY
FXPE10-10M*		10GbE OM3		AQUA	0.25dB	26dB	AQUA
FXOPE10-10M*		OPTIMIZED 10GbE OM3			0.15dB	26dB	
FZPE10-10M*		10GbE OM4		AQUA	0.25dB	26dB	AQUA
FZOPE10-10M*		OPTIMIZED 10GbE OM4			0.15dB	26dB	
F9PE10-10M*		9/125um OS1		YELLOW	0.35dB	55dB	BLUE

\* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-11				



THIRD ANGLE  
PROJECTION



**PANDUIT**<sup>TM</sup>  
CORP.  
TINLEY PARK, ILL 60477

ALL DIMENSIONS ARE GIVEN IN INCHES  
UNLESS OTHERWISE SPECIFIED.

DIMENSIONAL TOLERANCES ARE:  
 (.X) ±.03 | (.XXX) ±.010 | (.3) ±.008 | ANGLES

DRAWING FILENAME  
M02779BC\_DC/01A

SCALE  
NONE

PART NO.  
SEE SHEETS 2, 3 & 4

DRAWING NO.  
02779-11  
SHEET 3 OF 4

SIZE  
A

DRAWN BY: MC      REVIEW DRAWING NUMBERS:

DATE: 04-27-07

CHK'D: RAF

FIBER OPTIC PATCH CORD  
DUPLEX LC TO LC CONFIGURATION  
CUSTOMER DRAWING



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX LC TO LC FIBER OPTIC PATCH CORD							
PANDUIT PART NO.	CABLE				LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5LE10-10M*	LOW SMOKE ZERO HALOGEN (LSZH) IEC	50/125um OM2	DUPLEX 1.6mm ZIPCORD	ORANGE	0.25dB	20dB	BLACK
F6LE10-10M*		62.5/125um OM1					ELECTRIC IVORY
FXLE10-10M*		10GbE OM3		AQUA	0.25dB	26dB	AQUA
FXOLE10-10M*		OPTIMIZED 10GbE OM3			0.15dB	26dB	
FZLE10-10M*		10GbE OM4		AQUA	0.25dB	26dB	AQUA
FZOLE10-10M*		OPTIMIZED 10GbE OM4			0.15dB	26dB	
F9LE10-10M*		9/125um OS1		YELLOW	0.35dB	55dB	BLUE

\* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-11				

		<b>PANDUIT</b> <sup>TM</sup> CORP. TINLEY PARK, ILL 60477	
 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03   (.XXX) ±.010   (.3) ±.008   ANGLES	
DRAWN BY MC		REVIEW DRAWING NUMBERS	
DATE 04-27-07		DRAWING FILENAME M02779BC_DC/01A	
CHK'D RAF		SCALE NONE	
		PART NO. SEE SHEETS 2, 3 & 4	
		DRAWING NO. 02779-11	
		SHEET 4 OF 4	
		SIZE <b>A</b>	