



PANDUIT PART NUMBER	WEIGHT
FR12TB2412 FR12TB2412M	4.49 LB/EACH (2037g/EACH)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET FOR 24" WIDE CABLE PATHWAYS IS USED TO SUPPORT THE FIBERRUNNER 12x4 CABLE ROUTING SYSTEM BETWEEN TWO (2) SECTIONS OF NEW 1/2" (M12) THREADED ROD THAT ARE 24" (609.6) - 31.5" (800.1) APART.
3. THE FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET FOR 24" WIDE CABLE PATHWAYS - 1/2" (M12) THREADED ROD INCLUDES:
ONE (1) BRACKET ASSEMBLY,
TWO (2) 1/2 CLAMP PLATES,
FOUR (4) 1/2 HELICAL SPRING LOCKWASHERS,
FOUR (4) 1/2-13 HEAVY HEX NUTS (FR12TB2412 ONLY),
FOUR (4) M12x1.75 HEX NUTS (FR12TB2412M ONLY),
ONE (1) 1/4-20 T-BOLT,
ONE (1) 1/4-20 HEX KEPS NUT.
4. FINISH COLOR: BLACK (EXCEPT FOR HARDWARE)
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D39701CS_DC/00 FR12TB2412

CAD FILENAME/LAYERS		FR12TB2412.pdf	
PANDUIT CORP		TINLEY PARK, ILLINOIS	
FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET FOR 24" WIDE CABLE PATHWAYS - 1/2" (M12) THREADED ROD (FR12TB2412, FR12TB2412M) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY MSO	MAT'L: STEEL	SCALE NONE	
DATE 10-21-08		DRAWING NO. 39701 - 48	DWG A
CHK'D SL			SIZE

R	10-21-08	MSO	SL	RELEASED TO PRODUCTION	39701-48	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	GMBH	