

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


DUPLEX LC TO LC FIBER OPTIC PATCH CORD

PANDUIT PART NUMBER	LENGTH (**) M = METERS	CABLE				LC CONNECTOR		
		FIBER TYPE	COUNT	RATING	COLOR	BOOT COLOR	MAX. IL	MIN. RL
NKF6ER02L-LM**	01, 02, 03, 05, 10	62.5/125 OM1	DUPLEX 1.6mm ZIPCORD	RISER (OFNR)	ORANGE	WHITE	0.75dB	26dB
NKF5ER02L-LM**		50/125 OM2				BLACK		
NKFXER02L-LM**		50/128 OM3				AQUA		
NKF9ER02L-LM**		SINGLEMODE OS1				WHITE		40dB
NKF6EL02L-LM**		62.5/125 OM1		LOW SMOKE ZERO HALOGEN (LSZH)	ORANGE	WHITE	0.75dB	26dB
NKF5EL02L-LM**		50/125 OM2				BLACK		
NKFXEL02L-LM**		50/128 OM3				AQUA		
NKF9EL02L-LM**		SINGLEMODE OS1				WHITE		40dB

NETKEY FIBER OPTIC PATCH CORD
DUPLEX LC TO LC CONFIGURATION
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



THIRD ANGLE
PROJECTION
DRAWN BY EFK

DATE
12-14-09

CHK'D

ALL DIMENSIONS ARE GIVEN IN INCHES
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX) ±.010 (0.3)
(.XX) ±.03 (0.8) ANGLES

MATERIAL

DRAWING FILENAME
M01302CR_DC/00A

SCALE
NONE

PART NO. NKF•ER02L-LM••
NKF•EL02L-LM••

DRAWING NO.
01302-52
SHEET 2 OF 2
SIZE
A

R	12-14-09	EFK		RELEASED TO PRODUCTION	01302-52				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	OTH