

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


DUPLEX SC TO LC FIBER OPTIC PATCH CORD

PANDUIT PART NUMBER	LENGTH (**) M = METERS	CABLE				CONNECTORS		
		FIBER TYPE	COUNT	RATING	COLOR	BOOT COLOR	MAX. IL	MIN. RL
NKF6ER02S-LM**	01, 02, 03, 05, 10	62.5/125 OM1	DUPLEX 1.6mm ZIPCORD	RISER (OFNR)	ORANGE	WHITE	0.75dB	26dB
NKF5ER02S-LM**		50/125 OM2				BLACK		
NKFXER02S-LM**		50/125 OM3				AQUA		
NKF9ER02S-LM**		SINGLEMODE OS1				WHITE		40dB
NKF6EL02S-LM**		62.5/125 OM1		LOW SMOKE ZERO HALOGEN (LSZH)	ORANGE	WHITE	0.75dB	26dB
NKF5EL02S-LM**		50/125 OM2				BLACK		
NKFXEL02S-LM**		50/125 OM3				AQUA		
NKF9EL02S-LM**		SINGLEMODE OS1				WHITE		40dB

NETKEY FIBER OPTIC PATCH CORD
DUPLEX SC TO LC CONFIGURATION
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ±.03 (0.8) ANGLES
(.XXX) ±.010 (0.3)

DRAWING FILENAME
M01302CT_DC/00B

SCALE
NONE

DRAWN BY
EFK

MATERIAL

PART NO. NKF•ER02S-LM••
NKF•EL02S-LM••

DATE
12-14-09

DRAWING NO.
01302-54
SHEET 2 OF 2

CHK'D
WMA

01	07-28-11	EFK	PJB	RELEASED TO PRODUCTION	01302-54	RWB			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	