



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Panduit Part Number	Color	CABLE SIZE	Dimension	
			"B"	"L"
NWSLC-2Y	YELLOW	2 mm SIMPLEX FIBER OPTIC	0.28 [7.11]	1.25 [31.75]
NWSLC-3Y	ORANGE	3 mm SIMPLEX FIBER OPTIC	0.30 [7.62]	1.25 [31.75]
NWSLC-7Y	WHITE	3 mm DUPLEX FIBER OPTIC	0.39 [9.91]	1.25 [31.75]
△2 NWSLC-2Y-AQ	AQUA	2 mm SIMPLEX FIBER OPTIC	0.28 [7.11]	1.25 [31.75]
△2 NWSLC2-2Y	YELLOW	2 mm SIMPLEX 10 GIG FIBER OPTIC	0.28 [7.11]	2.25 [57.15]
△2 NWSLC2-3Y	ORANGE	3 mm SIMPLEX FIBER OPTIC	0.30 [7.62]	2.25 [57.15]
△2 NWSLC2-7Y	WHITE	3 mm DUPLEX FIBER OPTIC	0.39 [9.91]	2.25 [57.15]
△2 NWSLC2-2Y-AQ	AQUA	2 mm SIMPLEX 10 GIG FIBER OPTIC	0.28 [7.11]	2.25 [57.15]



CAD FILENAME/LAYERS 100619QY-DC-C10098/02C

PANDUIT CORP. TINLEY PARK, ILLINOIS

NWSLC-\*Y & NWSLC2-\*Y LABEL CORE CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
 (.X) ± (.XXX) ±  
 (.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	9/9/11	RVU		Add NWSLC2-2Y, NWSLC2-3Y, NWSLC2-7Y, AND NWSLC2-2Y-AQ. ADD NWSLC-2Y-AQ.	6508		R	
1	11/2/10	RVU		ADD "Y" TO PART NUMBERS. USE "B" INSTEAD OF "A" SIMILAR TO CONTROL DWG.	6217		R	
0	9-23-03	RVU		DRAWING RELEASE	3420		R	

DRAWN BY RVU  
 DATE 9-23-03  
 CH *[Signature]*

MAT'L: FLEXIBLE PVC

SCALE NTS  
 DRAWING NO. C10098  
 DWG SIZE A