

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TWIST TIE

NOTES:

- **1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.

- TERMINATED WITH (8 POSITION) MODULAR PLUGS AT BOTH ENDS PER T568B.



- CONSTRUCTED WITH STRANDED CAT6 UTP 24AWG CM PATCH CABLE

- MATERIALS:

PLUG: POLYCARBONATE

BOOT: CLEAR PVC



- NOMINAL CABLE JACKET DIAMETER IS 0.235 IN (5.97MM)



STRAIN RELIEF BOOT

T568B WIRING SCHEME

PLUG POSITION:

1
2
3
4
5
6
7
8

CABLE WIRE:
WHITE/ORANGE
ORANGE
WHITE/GREEN
BLUE
WHITE/BLUE
GREEN
WHITE/BROWN
BROWN



CABLE COLORS	** = COLOR
OFF WHITE	--
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR
ORANGE	OR
VIOLET	VL

SEE SHEET 2 FOR
PATCH CORD LENGTHS
AND PART NUMBERS

IDENTIFICATION
LABEL



TANGLE-FREE
LATCH




MODULAR PLUG



PLUG POSITION 1

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
2	5-14-10	BJN		K. ADDED TANGLE-FREE LATCH J. ADDED IDENTIFICATION LABEL H. ADDED NEW NOTE 6 I. ADDED (I) TO P/N	02479-360				
1	4-23-07	BJN	EJH	G. ADDED STRAIN RELIEF BOOT F. TX6 PLUS UTP WAS TX-6™ PLUS CATEGORY 6 E. ADDED MODULAR PLUG C. ADDED COLOR TABLE D. ADDED CABLE LG A. ADDED SH2 B. ADDED NOTES 3-5	02479-360		REGA		
R	3-28-06	NER	WJC	RELEASED TO PRODUCTION	02479-360		RMD		


MODEL FILENAME M01185AC/06		SIZE A
DRAWING FILENAME M02479NV_DC360/00C		
TITLE TX6 PLUS UTP PATCH CORDS (CM) CUSTOMER DRAWING		
 PANDUIT ^R CORP. TINLEY PARK, IL 60477		I.I. NUMBER
 THIRD ANGLE PROJECTION		PRODUCT SPEC
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		WORK INSTRUCTION
DRAWN BY NER		SCALE NONE
DATE 3-28-06		PART NO. UTPSPXX**(Y) 1
CHK'D WJC		DRAWING NO. 02479-360 SHEET 1 OF 2

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TX6 PLUS UTP PATCH CORDS

PANDUIT PART NUMBER	MIN. CABLE LENGTH	PANDUIT PART NUMBER	MIN. CABLE LENGTH
UTPSP1**Y	1 FT.	UTPSP0.5M**Y	0.5 METER
UTPSP2**Y	2 FT.	UTPSP1M**Y	1 METER
UTPSP3**Y	3 FT.	UTPSP1.5M**Y	1.5 METER
UTPSP4**Y	4 FT.	UTPSP2M**Y	2 METERS
UTPSP5**Y	5 FT.	UTPSP2.5M**Y	2.5 METERS
UTPSP6**Y	6 FT.	UTPSP3M**Y	3 METERS
UTPSP7**Y	7 FT.	UTPSP4M**Y	4 METERS
UTPSP8**Y	8 FT.	UTPSP5M**Y	5 METERS
UTPSP9**Y	9 FT.	UTPSP6M**Y	6 METERS
UTPSP10**Y	10 FT.	UTPSP7M**Y	7 METERS
UTPSP11**Y	11 FT.	UTPSP8M**Y	8 METERS
UTPSP12**Y	12 FT.	UTPSP9M**Y	9 METERS
UTPSP13**Y	13 FT.	UTPSP10M**Y	10 METERS
UTPSP14**Y	14 FT.	UTPSP15M**Y	15 METERS
UTPSP15**Y	15 FT.	UTPSP20M**Y	20 METERS
UTPSP16**Y	16 FT.	UTPSP25M**Y	25 METERS
UTPSP17**Y	17 FT.	UTPSP30M**Y	30 METERS
UTPSP18**Y	18 FT.	UTPSP35M**Y	35 METERS
UTPSP19**Y	19 FT.	UTPSP40M**Y	40 METERS
UTPSP20**Y	20 FT.		
UTPSP25**Y	25 FT.		
UTPSP30**Y	30 FT.		
UTPSP35**Y	35 FT.		
UTPSP40**Y	40 FT.		



MODEL FILENAME		M01185AC/06		SIZE
DRAWING FILENAME		M02479NV_DC360/00C		A
TITLE TX6 PLUS UTP PATCH CORDS (CM) CUSTOMER DRAWING				
		PANDUIT ^R CORP. TINLEY PARK, IL 60477		I.I. NUMBER
		ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		PRODUCT SPEC
DRAWN BY NER		REVIEW DRAWING NUMBERS		WORK INSTRUCTION
DATE 3-28-06		PART NO. UTPSPXX** (Y)		SCALE NONE
CHK'D WJC		DRAWING NO. 02479-360 SHEET 2 OF 2		

2	5-13-10	BJN		SEE SHEET 1 FOR REVISIONS	02479-360				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH